## **Product datasheet**

Specification





# ClimaSys PTC heating resistance 100W 110-250V

Local distributor code:

1915932 NSYCR100WU2

EAN Code: 3606480152191

#### Overview

Lead Time Usually Ships within 4 Weeks

#### Main

| Range                     | ClimaSys             |  |
|---------------------------|----------------------|--|
| Product Name              | ClimaSys CR          |  |
| Product Or Component Type | Resistance heater    |  |
| Range Compatibility       | Prisma P<br>Prisma G |  |
| Power Range               | 90 W                 |  |
| Input Voltage             | 110250 V AC 50/60 Hz |  |

## Complementary

| Operating Position                    | Vertical   |
|---------------------------------------|--|
| Ambient Air Temperature For Operation | -4070 °C   |
| Ip Degree Of Protection               | IP20   |
| Product Certifications                | UL<br>VDE  |
| Material                              | Body: extruded aluminium   |
| Height                                | 200 mm   |
| Width                                 | 85 mm  |
| Depth                                 | 65 mm  |
| Condition Of Use                      | Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed |
| Fixing Mode                           | By clips   |
| Mounting Support                      | 35 mm DIN rail   |

## **Packing Units**

| Unit Type Of Package 1       | PCE       |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 6.500 cm  |
| Package 1 Width              | 8.000 cm  |
| Package 1 Length             | 20.500 cm |
| Package 1 Weight             | 544.000 g |

| Unit Type Of Package 2       | S04       |
|------------------------------|-----------|
| Number Of Units In Package 2 | 16        |
| Package 2 Height             | 30.000 cm |
| Package 2 Width              | 40.000 cm |
| Package 2 Length             | 60.000 cm |
| Package 2 Weight             | 9.472 kg  |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant with Exemptions   |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information                         |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations  |