

Product datasheet

Specifications



ClimaSys Exchanger air-water 6000W sides of enclosure

Local distributor code:
402654054

NSYCEW6KUL

 **Discontinued on:** 14 Feb 2023

EAN Code: 3606480653407

 **Discontinued**

Main

Range	ClimaSys
Product Name	ClimaSys CE
Product Or Component Type	Air-water exchanger
Mounting Type	Sides of enclosure
Cooling Power	6000 W

Complementary

Pressure	8 bar for water
Pressure Drop	0.5 bar
Water Flow	Internal circuit: 800 l/h
Flow Rate	External circuit: 1450 m3/h
Control Type	Thermostat
Temperature Setting Range	20...46 °C
Ambient Air Temperature For Operation	1...70 °C outside the enclosure: 20...60 °C inside the enclosure:
Controlled Fluid	Water
Fluid Connection Type	G 1/2 (female)
Input Voltage	230 V 50/60 Hz
[In] Rated Current	0.71 A
Power Consumption In W	160 W
Height	1500 mm external:
Width	450 mm external:
Depth	163 mm external:
Net Weight	40 kg
Noise Level	69 dB
Protection Type	Thermal protection: T 2 A
Material	Steel
Colour	Grey (RAL 7035)

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit)
	IP55 conforming to IEC 60529 (on the external circuit)
Product Certifications	UL
Standards	DIN 3168

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
<hr/>		
Eu Rohs Directive		Compliant EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
<hr/>		
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<hr/>		