Product datasheet

Specification





ClimaSys standard cooling unit roof of enclosure - 2050W at 400 V

Local distributor code:

402654423

NSYCU2K3P4R

Discontinued on: 23 Nov 2023

! End-of-service on: 23 Feb 2024

(!) Discontinued

EAN Code: 3606480620942

Main

Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Roof of enclosure	
Installation	Indoor roof	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	400 V AC at 50/60 Hz, 3 phases	
Rated Power	2050 W	
Cooling Power	2050 W 50/60 Hz L35-L35 1560 W 50/60 Hz L35-L50	

Complementary

Height	415 mm	
Width	567 mm	
Depth	401 mm	
[In] Rated Current	1.9 A	
Inrush Current	10 A	
Power Consumption In W	990 W at 50/60 Hz, L35-L35 1190 W at 50/60 Hz, L35-L50	
Energy Efficiency Ratio	2.1	
Control Type	Electronic controller	
Temperature Setting Range	2055 °C	
Ambient Air Temperature For Operation	2046 °C inside the enclosure: 2050 °C outside the enclosure: 55 °C maximum:	
Noise Level	65 dB conforming to EN/ISO 3746	
Pressure	25 bar	
Flow Rate	External circuit: 1820 m3/h at 50/60 Hz Internal circuit: 1050 m3/h at 50/60 Hz	
Net Weight	52 kg	
Cooling Gas Type	R134a (0.55 kg)	

Type Of Filter	Optional external circuit filter	
Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):	
Material	Steel	
Colour	Grey (RAL 7035)	

Environment

Product Certifications	CE
Directives	2006/95/EC - low voltage directive 2006/42/EC - machinery 2004/108/EC - electromagnetic compatibility
Standards	EN 60204-1 EN/ISO 12100 EN 60335-1 EN 378 EN 60335-2-40
Ip Degree Of Protection	IP34 conforming to IEC 60529 (on the external circuit) IP54 conforming to IEC 60529 (on the internal circuit)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	46.5 cm
Package 1 Width	50.0 cm
Package 1 Length	63.0 cm
Package 1 Weight	53.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	66.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	120.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information