Product datasheet

Specifications





ClimaSys PTC heating resistance 10W, 12-24V Local distributor code:

398243317

NSYCR10WU1

EAN Code: 3606480152108

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Resistance heater
Power Range	10 W
Input Voltage	1224 V DC
Electrical Connection	Cable 2 x 0.75 mm ² length: 300 mm

Complementary

Operating Position	Vertical
Ambient Air Temperature For Operation	-4070 °C
Ip Degree Of Protection	IP20
Product Certifications	UL VDE
Material	Body: extruded aluminium
Height	External: 85 mm
Width	External: 25 mm
Depth	External : 57 mm
Condition Of Use	Electrical protection is needed Air sealed enclosure Heaters must be installed with a thermal controller
Fixing Mode	By clips
Mounting Support	35 mm DIN rail

Packing Units

<u>~</u>	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	8 cm
Package 1 Length	13 cm
Package 1 Weight	120 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	50
Package 2 Height	21 cm

Package 2 Width	40.5 cm
Package 2 Length	30 cm
Package 2 Weight	7 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations