



ClimaSys PTC heating resistance 10W, 12-24V insulate

Local distributor code: 388826388

NSYCR10WU1C

EAN Code: 3606480152245

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Resistance heater
Power Range	10 W
Input Voltage	1224 V DC
Electrical Connection	2 screw terminals 2.5 mm ²

Complementary

Operating Position	Vertical
Ambient Air Temperature For Operation	-4070 °C
Ip Degree Of Protection	IP20
Electrical Insulation Class	Class II
Product Certifications	VDE
Material	Body: extruded aluminium Cover: plastic
Height	External: 98 mm
Width	External: 38 mm
Depth	External : 75 mm
Condition Of Use	Air sealed enclosure Heaters must be installed with a thermal controller Electrical protection is needed
Fixing Mode	By clips
Mounting Support	35 mm DIN rail

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8 cm
Package 1 Length	11.5 cm
Package 1 Weight	176 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	80

Package 2 Height	16 cm	
Package 2 Width	29 cm	
Package 2 Length	37 cm	
Package 2 Weight	14.08 kg	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations