Product datasheet

Specifications



ClimaSys standard cooling unit roof of enclosure - 2050W at 400 V

Local distributor code: 402654436

NSYCU2K3P4RUL

() Discontinued on: 9 Feb 2023

EAN Code: 3606480654053

① Discontinued

Main

Range	ClimaSys
Product Name	CU
Product Or Component Type	Cooling unit
Mounting Type	Roof of enclosure
Installation	Indoor roof
Product Destination	For enclosure
Mounting Mode	By screws
Supply Voltage	460 V AC at 60 Hz, 3 phases
Rated Power	2300 W
Cooling Power	6990 Btu/h 60 Hz L35-L35 5320 Btu/h 60 Hz L35-L50

Complementary

Height	415 mm
Width	567 mm
Depth	401 mm
[In] Rated Current	1.9 A
Inrush Current	10 A
Power Consumption In W	990 W at 60 Hz, L35-L35 1190 W at 60 Hz, L35-L50
Energy Efficiency Ratio	2.1
Control Type	Electronic controller
Temperature Setting Range	2045 °C
Ambient Air Temperature For Operation	2045 °C outside the enclosure: 45 °C maximum: 2045 °C inside the enclosure:
Noise Level	65 dB
Pressure	25 bar
Flow Rate	External circuit: 1820 m3/h at 60 Hz Internal circuit: 1050 m3/h at 60 Hz
Net Weight	52 kg
Cooling Gas Type	R134a (0.55 kg)
Type Of Filter	Optional external circuit filter

Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):
Material	Steel
Colour	Grey (RAL 7035)

Environment

Product Certifications	UL
Standards	DIN 3168
Ip Degree Of Protection	IP34 conforming to IEC 60529 (on the external circuit) IP54 conforming to IEC 60529 (on the internal circuit)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	40.1 cm
Package 1 Width	41.5 cm
Package 1 Length	56.7 cm
Package 1 Weight	52.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	4
Package 2 Height	63.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	234.4 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information