# **Product datasheet**

Specifications





# ClimaSys standard cooling unit side of enclosure - 3850W at 400 V

Local distributor code:

402654517 NSYCU4K3P4

! Discontinued on: 23 Nov 2023

! End-of-service on: 23 Feb 2024

EAN Code: 3606480620898

#### Main

Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Side	
Installation	Indoor side	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	400 V AC at 50/60 Hz, 3 phases	
Rated Power	3850 W	
Cooling Power	3850 W 50/60 Hz L35-L35 2870 W 50/60 Hz L35-L50	

#### Complementary

Height	1270 mm
Width	500 mm
Depth	336 mm
[In] Rated Current	3.6 A
nrush Current 18 A	
Power Consumption In W	1780 W at 50/60 Hz, L35-L35 2050 W at 50/60 Hz, L35-L50
Energy Efficiency Ratio	2.2
Control Type	Electronic controller
Temperature Setting Range	2050 °C
Ambient Air Temperature For Operation	50 °C maximum: 2046 °C inside the enclosure: 2050 °C outside the enclosure:
Noise Level	70 dB conforming to EN/ISO 3746
Pressure	25 bar
Flow Rate	Internal circuit: 1450 m3/h at 50/60 Hz External circuit: 1450 m3/h at 50/60 Hz
Net Weight	85 kg

Cooling Gas Type	R134a (1.14 kg)	
Type Of Filter	Optional external circuit filter	
Protection Type	Thermal protection: T 8 A Short-circuit protection (magnetic):	
Material	Steel	
Colour	Grev (RAL 7035)	

## **Environment**

<b>Product Certifications</b>	CE
Directives	2004/108/EC - electromagnetic compatibility 2006/42/EC - machinery 2006/95/EC - low voltage directive
Standards	EN 60335-2-40 EN 378 EN 60204-1 EN/ISO 12100 EN 60335-1
Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit)

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33.6 cm
Package 1 Width	50.0 cm
Package 1 Length	127.0 cm
Package 1 Weight	85.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	160.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	225.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information