Product datasheet





ClimaSys standard cooling unit roof of enclosure - 3850W at 400 V

Local distributor code:

402654546

NSYCU4K3P4RUL

! Discontinued on: 9 Feb 2023

EAN Code: 3606480654107

! Discontinued

Main

| Range | ClimaSys | |
|---------------------------|---|--|
| Product Name | CU | |
| Product Or Component Type | Cooling unit | |
| Mounting Type | Roof of enclosure | |
| Installation | Indoor roof | |
| Product Destination | For enclosure | |
| Mounting Mode | By screws | |
| Supply Voltage | 460 V AC at 60 Hz, 3 phases | |
| Rated Power | 4300 W | |
| Cooling Power | 13140 Btu/h 60 Hz L35-L35 9790 Btu/h 60 Hz L35-L50 | |

Complementary

| Height | 496 mm |
|---|---|
| Width | 797 mm |
| Depth | 492 mm |
| [In] Rated Current | 3.6 A |
| Inrush Current | 17 A |
| Power Consumption In W | 1790 W at 60 Hz, L35-L35 2010 W at 60 Hz, L35-L50 |
| Energy Efficiency Ratio | 2.2 |
| Control Type | Electronic controller |
| Temperature Setting Range | 2045 °C |
| Ambient Air Temperature For Operation | 2045 °C outside the enclosure: 45 °C maximum: 2045 °C inside the enclosure: |
| Noise Level | 75 dB |
| Pressure | 25 bar |
| Flow Rate External circuit: 3410 m3/h at 60 Hz Internal circuit: 1450 m3/h at 60 Hz | |
| Net Weight | 86 kg |
| Cooling Gas Type | R134a (1.6 kg) |
| Type Of Filter Optional external circuit filter | |

| Protection Type | Thermal protection: T 6 A Short-circuit protection (magnetic): |
|-----------------|--|
| Material | Steel |
| Colour | Grey (RAL 7035) |

Environment

| Product Certifications | UL |
|-------------------------|---|
| Standards | DIN 3168 |
| Ip Degree Of Protection | IP34 conforming to IEC 60529 (on the external circuit) IP54 conforming to IEC 60529 (on the internal circuit) |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 49.2 cm |
| Package 1 Width | 49.6 cm |
| Package 1 Length | 79.7 cm |
| Package 1 Weight | 86.0 kg |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 85.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 212.2 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ⊘ | Toxic Heavy Metal Free | |
| Ø | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |