

Product datasheet

Specifications



ClimaSys indoor slim cooling unit block - 1500W at 400 V - UL

Local distributor code:
402656324

NSYCUS1K52P4UL

Discontinued on: 9 Feb 2023

EAN Code: 3606480676963

Discontinued

Main

Range	ClimaSys
Product Name	CU
Product Or Component Type	Slim cooling unit block
Mounting Type	Door of enclosure
Installation	Indoor side
Product Destination	For enclosure
Mounting Mode	By screws
Supply Voltage	460 V AC at 60 Hz, 2 phases 400...460 V AC at 50/60 Hz
Rated Power	1500 W
Cooling Power	5118 Btu/h 50/60 Hz L35-L35 3924 Btu/h 50/60 Hz L35-L50

Complementary

Height	1696 mm
Width	495 mm
Depth	195 mm
[In] Rated Current	3.2 A
Inrush Current	11 A
Power Consumption In W	970 W at 50/60 Hz, L35-L50 840 W at 50/60 Hz, L35-L35
Energy Efficiency Ratio	1.8
Control Type	Electronic controller
Temperature Setting Range	20...50 °C
Ambient Air Temperature For Operation	50 °C maximum: 20...46 °C inside the enclosure: 20...50 °C outside the enclosure:
Noise Level	66 dB conforming to EN/ISO 3746
Pressure	28 bar
Flow Rate	External circuit: 860 m3/h at 50/60 Hz Internal circuit: 860 m3/h at 50/60 Hz
Net Weight	57 kg
Cooling Gas Type	R134a (0.46 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Type Of Filter	Optional external circuit filter
Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):
Material	Steel
Colour	Grey (RAL 7035)

Environment

Product Certifications	UL
Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit) IP34 conforming to IEC 60529 (on the external circuit)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	60.0 cm
Package 1 Width	80.0 cm
Package 1 Length	191.0 cm
Package 1 Weight	85.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	201.5 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	186.6 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information