Product datasheet





ClimaSys standard cooling unit roof of enclosure - 820W at 230 V

Local distributor code:

402657226

NSYCUX800R

! Discontinued on: 9 Feb 2023

EAN Code: 3606480653988

! Discontinued

Main

Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Roof of enclosure	
Installation	Indoor roof	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	230 V AC at 50/60 Hz, 1 phase	
Rated Power	820 W	
Cooling Power	820 W 50/60 Hz L35-L35 680 W 50/60 Hz L35-L50	

Complementary

Height	340 mm	
Width	600 mm	
Depth	340 mm	
[In] Rated Current	2.9 A	
Inrush Current	12 A	
Power Consumption In W	510 W at 50/60 Hz, L35-L35 560 W at 50/60 Hz, L35-L50	
Energy Efficiency Ratio	1.6	
Control Type	Electronic controller	
Temperature Setting Range	2055 °C at 50 Hz 2050 °C at 60 Hz	
Ambient Air Temperature For Operation	2046 °C inside the enclosure: 55 °C maximum: 2055 °C at 50 Hz outside the enclosure: 2050 °C at 60 Hz outside the enclosure:	
Noise Level	65 dB conforming to EN/ISO 3746	
Pressure	25 bar	
Flow Rate	Internal circuit: 570 m3/h at 50/60 Hz External circuit: 860 m3/h at 50/60 Hz	
Net Weight	23 kg	
Cooling Gas Type	R134a (0.31 kg)	

Type Of Filter	Optional external circuit filter
Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):
Material	Stainless steel
Colour	Grey (RAL 7035)

Environment

Product Certifications	CE	
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive 2006/42/EC - machinery	
Standards	EN/ISO 12100 EN 60204-1 EN 378 EN 60335-2-40 EN 60335-1	
Ip Degree Of Protection	IP34 conforming to IEC 60529 (on the external circuit) IP54 conforming to IEC 60529 (on the internal circuit)	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	34.0 cm
Package 1 Width	34.0 cm
Package 1 Length	60.0 cm
Package 1 Weight	45.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	179.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	285.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information