

Product datasheet

Specifications



ClimaSys forced vent. IP54, 300m3/h, 48V DC, with outlet grille and filter G2

Local distributor code:
388829440

NSYCVF300M48DPF

EAN Code: 3606480151316

Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Standard
Flow Rate	Free flow rate with standard filter: 262 m3/h
[Us] Rated Supply Voltage	25...60 V
Input Voltage	48 V DC

Complementary

Absorbed Power	11 W
[In] Rated Current	0.24 A
Noise Level < At	55...56 dB
Bearing Type	Ball
Height	External: 268 mm
Width	External: 248 mm
Depth	External : 103.4 mm
Cut-Out Dimensions	223 x 223 mm
Net Weight	1.1 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient Air Temperature For Operation	-10...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Maximum Pressure	158 Pa flow rate 0 m³/h
Connections - Terminals	Cable
Ip Degree Of Protection	IP54
Device Composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 filter: front of axial motor 1 outlet grille: front 1 cut-out template 1 power cord

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Condition Of Use	Surrounding environment must be relatively clean Filter must be cleaned and replaced regularly Flow rates depends on the work point, see ProClima software Outside temperature must be 5 °C lower than inside temperature Overfrequent filter replacement should be avoided
------------------	---

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18 cm
Package 1 Width	25 cm
Package 1 Length	28 cm
Package 1 Weight	1.36 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	50
Package 2 Height	100 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	83 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information