# **Product datasheet**





## ClimaSys forced vent. IP54, 38m3/ h, 48V DC, with outlet grille and filter G2

Local distributor code: 388829385

NSYCVF38M48DPF

! Discontinued on: 9 Feb 2023

! Discontinued

EAN Code: 3606480151194

#### Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Standard
Flow Rate	Free flow rate with standard filter: 44 m3/h
[Us] Rated Supply Voltage	3656 V
Input Voltage	48 V DC

### Complementary

Absorbed Power	3.6 W
[In] Rated Current	0.07 A
Noise Level < At	4041 dB
Bearing Type	Ball
Height	External: 137 mm
Width	External: 117 mm
Depth	External : 49 mm
Cut-Out Dimensions	92 x 92 mm
Net Weight	0.23 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient Air Temperature For Operation	-1070 °C
Ambient Air Temperature For Storage	-4070 °C
Maximum Pressure	29 Pa flow rate 0 m³/h
Connections - Terminals	Cable
Ip Degree Of Protection	IP54
Device Composition	1 axial motor

2 protective grille: on the front and rear surfaces

1 filter: front of axial motor

1 outlet grille: front

1 cut-out template

Condition Of Use

Outside temperature must be 5 °C lower than inside temperature
Surrounding environment must be relatively clean
Overfrequent filter replacement should be avoided
Flow rates depends on the work point, see ProClima software

Filter must be cleaned and replaced regularly

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15 cm
Package 1 Width	15 cm
Package 1 Length	10 cm
Package 1 Weight	265 g

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information