Product datasheet

Specification





ClimaSys forced vent. IP54, 560m3/h, 115V, with outlet grille and filter G2

Local distributor code: 388827617

NSYCVF560M115PF

EAN Code: 3606480151330

Overview

Lead Time Usually Ships within 4 Weeks

Main

| Range | ClimaSys | |
|---------------------------|--|--|
| Product Name | ClimaSys CV | |
| Product Or Component Type | Fan | |
| Type Of Filter | Standard | |
| Flow Rate | Free flow rate with standard filter: 562 m3/h at 50 Hz Free flow rate with standard filter: 586 m3/h at 60 Hz | |
| [Us] Rated Supply Voltage | 103122 V | |
| Input Voltage | 115 V 50/60 Hz | |

Complementary

| 65 W 50 Hz 83 W 60 Hz |
|--|
| 03 W 00 112 |
| 0.6 A 50 Hz |
| 0.72 A 60 Hz |
| 59 dB |
| Ball |
| External: 336 mm |
| External: 316 mm |
| External : 161 mm |
| 291 x 291 mm |
| 3.2 kg |
| Outlet grille: injected thermoplastic (ASA PC) |
| Outlet grille: grey (RAL 7035) |
| -1560 °C |
| -4070 °C |
| 140 Pa flow rate 0 m³/h |
| Terminal block |
| IP54 |
| |

| Device Composition | axial motor protective grille: on the front and rear surfaces filter: front of axial motor outlet grille: front | |
|---|---|--|
| | | |
| | Condition Of Use | Outside temperature must be 5 °C lower than inside temperature |
| Overfrequent filter replacement should be avoided | | |
| Flow rates depends on the work point, see ProClima software | | |
| Filter must be cleaned and replaced regularly | | |
| Surrounding environment must be relatively clean | | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 23 cm |
| Package 1 Width | 32 cm |
| Package 1 Length | 34 cm |
| Package 1 Weight | 3.696 kg |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 68 |
| Package 2 Height | 180 cm |
| Package 2 Width | 100 cm |
| Package 2 Length | 120 cm |
| Package 2 Weight | 264 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |