Product datasheet

Specification





Spacial SF/SM mounting plate - 1400x1000 mm

Local distributor code:

383556035

NSYMP1410

EAN Code: 3606485130682

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Device Composition	1 mounting plate 2 sliding shoes
Quantity Per Set	Set of 1
Material	Galvanised steel

Complementary

Fixing Mode	By fixing brackets
Maximum Load	300 kg/m²
Permanent Permissible Load	500 kg intermediate position 600 kg back of the enclosure
Height	Fixing centers: 1250 mm Nominal: 1400 mm Real: 1297 mm
Width	Fixing centers: 850 mm Nominal: 1000 mm Real: 896 mm
Depth	27 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	131.0 cm
Package 1 Width	91.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	27.0 kg

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
Ø	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations