Product datasheet

Specifications





2 side panels for plinth. 300x100mm. Folded sheet steel. RAL 7022. IP 30. IK 10.

Local distributor code: 398323512

NSYSPS3100SD

EAN Code: 3606480287091

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Plinth side panel
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Device Composition	fixing elements 4 corner cover 2 side panel
Range Compatibility	Spacial Spacial SD Spacial Spacial S3D
Mounting Support	Front plinth

Complementary

Fixing Mode	By screws
Material	Sheet steel
Colour	Grey (RAL 7022)
Surface Finish	Epoxy-polyester powder
Height	100 mm
Width	Nominal: 300 mm
Depth	300 mm

Environment

Ip Degree Of Protection	IP30 (complete plinth)
Ik Degree Of Protection	IK10 (resistance to external mechanical impacts)

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	10.8 cm
Package 1 Length	11.3 cm
Package 1 Weight	574.0 g

Logistical informations

Country Of Origin

ES

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations