

# Product datasheet

Specifications



## Spacial SF/SM ventilated side plinth - 100x600x600 mm

Local distributor code:

398323745

NSYSPV6100

EAN Code: 3606485132570

### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Ventilated plinth side panel
Application	Electronic application Multi-purpose
Nominal Dimensions Of The Housing	-
Device Composition	fixing elements 4 corner cover 2 side panel
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Mounting Support	Front plinth

### Complementary

Fixing Mode	By screws
Colour	Grey (RAL 7022)
Surface Finish	Epoxy-polyester powder
Height	100 mm
Width	Nominal: 600 mm

### Environment

Ip Degree Of Protection	IP20 (complete plinth)
Ik Degree Of Protection	IK10

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	11.0 cm
Package 1 Length	45.0 cm
Package 1 Weight	4.62 kg

### Logistical informations

Country Of Origin	TN
-------------------	----

# Contractual warranty

---

Warranty

18 months

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

RoHS Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations