Specifications





on-delay timing relay - 0.1 s..100 h - 24 V AC - 4 OC

Local distributor code: 389834722

39834722 REXL4TMB7

EAN Code: 3389119400084

Main

Range Of Product	Harmony Timer Relays	
Product Or Component Type	Single function relay	
Fixing Mode	Plug-in (socket)	
Discrete Output Type	Relay	
Contacts Type And Composition	4 C/O	
Component Name	REXL	
Time Delay Type	Power on-delay	
Time Delay Range	660 s 110 s 110 h 110 min 660 min 10100 h 0.11 s	
Width	21 mm	

Complementary

•	
Contacts Material	Cadmium free
[Us] Rated Supply Voltage	24 V AC 50/60 Hz
Voltage Range	0.851.15 Us
[In] Rated Current	5 A AC
Repeat Accuracy	+/- 0.5 %
Setting Accuracy Of Time Delay	10 % at full scale at 25 °C conforming to IEC 61812-1
Temperature Drift	0.05 %/°C
Maximum Reset Time	250 ms after time delay, on de-energisation 50 ms during time delay, on de-energisation
Voltage Drift	+/- 0.2 %/V
Maximum Switching Capacity	4 x 5 A
Maximum Temporary Permissible Current	10 A for < 10 s
Minimum Switching Current	100 mA
Electrical Durability	100000 cycles at 250 V AC resistive
Mechanical Durability	10000000 cycles
Maximum Power Consumption	1.7 VA
[Ui] Rated Insulation Voltage	250 V conforming to IEC 255 Group C 250 V conforming to VDE 0010

Output Overvoltage Protection	2 J	
Surge Withstand	2 kV conforming to IEC 61000-4-5 level 3	
Creepage Distance	4 kV/3 conforming to IEC 60664-1	
Local Signalling	1 LED (red) for output in operation 1 LED (yellow) for power ON	
Number Of Functions	1	
Net Weight	0.05 kg	

Environment

Immunity To Microbreaks	5 ms
Dielectric Strength	2 kV for 1 mA/1 minute at 50 Hz conforming to IEC 60601-1 2 kV for 1 mA/1 minute at 50 Hz conforming to IEC 61812-1
Standards	IEC 60601-1 89/336/EEC IEC 61812-1 IEC 60601-2 73/23/EEC 93/68/EEC IEC 61000-6-2 EN 50081-2
Product Certifications	UL cUL
Ambient Air Temperature For Operation	-2060 °C
Ambient Air Temperature For Storage	-4070 °C
Ip Degree Of Protection	IP50 conforming to IEC 60529
Vibration Resistance	0.35 mm (f= 1055 Hz) conforming to IEC 60068-2-6
Relative Humidity	95 % without condensation conforming to IEC 60068-2-6
Resistance To Electrostatic Discharge	6 kV in contact conforming to IEC 61000-4-2 level 3 8 kV in air conforming to IEC 61000-4-2 level 3
Resistance To Electromagnetic Fields	10 V/m conforming to IEC 61000-4-3 level 3
Resistance To Fast Transients	2 kV conforming to IEC 61000-4-4 level 3
Immunity To Radioelectric Fields	10 V (0.1580 MHz) conforming to IEC 61000-4-6 level 3
Immunity To Voltage Dips	>= 95 % / 1 s conforming to IEC 61000-4-11 30 % / 10 ms conforming to IEC 61000-4-11 60 % / 100 ms conforming to IEC 61000-4-11
Disturbance Radiated/Conducted	Class B conforming to EN 55022 (EN 55011 group 1)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	3.000 cm
Package 1 Length	3.000 cm
Package 1 Weight	49.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	48
Package 2 Height	15.000 cm

Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.666 ka

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Width 21 mm





REXL4TMB7

Connections and Schema

Terminal Referencing




REXL4TMB7

Technical Description

Function A : Power on Delay Relay

Description

The timing period T begins on energisation. After timing, the outputs close. 4 Timed C/O Contacts $\,$



REXL4TMB7

Legend

