## **Product datasheet**

Specifications





# Interface plug-in relay, 10 A, 1 CO, lockable test button, LED, 48 V DC

Local distributor code:

403005738 RXG12ED

EAN Code: 3606480688744

## Main

| Range Of Product                                | Harmony Electromechanical Relays |  |
|---|----------------------------------|--|
| Series Name                                     | Interface relay                  |  |
| Product Or Component Type                       | Plug-in relay                    |  |
| Device Short Name                               | RXG                              |  |
| Contacts Type And Composition                   | 1 C/O                            |  |
| [Ithe] Conventional Enclosed<br>Thermal Current | 10 A at -4055 °C                 |  |
| Local Signalling                                | Flag                             |  |

## Complementary

| Status Led                     | With  |
|--------------------------------|---|
| [le] Rated Operational Current | 10 A at 30 V (DC) conforming to UL 10 A at 30 V (DC) conforming to IEC 10 A at 250 V (AC) conforming to IEC 10 A at 250 V (AC) conforming to UL |
| Electrical Durability          | 100000 cycles for NO resistive load at 55 °C 100000 cycles for NC resistive load at 55 °C   |
| Coil Resistance                | 4400 Ohm +/- 10 %   |
| Shock Resistance               | 20 gn in operation<br>100 gn not in operation   |
| Mounting Position              | Any position  |
| [Uc] Control Circuit Voltage   | 48 V DC   |
| Colour Of Cover                | Standard  |
| Drop-Out Voltage Threshold     | >= 0.1 Uc DC  |
| Load Current                   | 10 A at 250 V AC  |
| Minimum Switching Capacity     | 500 mW at 100 mA, 5 V DC  |
| Maximum Switching Capacity     | 2500 VA   |
| Control Type                   | Lockable test button  |
| Torque Value                   | 0.8 N.m   |
| Contact Resistance             | 100 mOhm  |
| Insulation Resistance          | 1000 MOhm at 500 V DC   |
| Electrical Insulation Class    | Class F   |
| Mechanical Durability          | 10000000 cycles   |
| Safety Reliability Data        | B10d = 100000   |

| Operating Time                | 20 ms  |
|-------------------------------|--|
| Reset Time                    | 20 ms  |
| Overvoltage Category          | III  |
| Maximum Switching Voltage     | 250 V AC<br>30 V DC  |
| Protection Category           | RTI  |
| Operating Rate                | <= 1800 cycles/hour under load<br><= 18000 cycles/hour no-load   |
| Pollution Degree              | 2  |
| Utilisation Coefficient       | 20 %   |
| [Ui] Rated Insulation Voltage | 250 V conforming to IEC<br>300 V conforming to CSA<br>300 V conforming to UL   |
| Dielectric Strength           | 1000 V AC between contacts with micro disconnection<br>5000 V AC between coil and contact with reinforced insulation |
| Test Levels                   | Level A group mounting   |
| Device Presentation           | Complete product   |
| Contacts Material             | Silver alloy (AgSnO2In2O3)   |
| Net Weight                    | 0.02 kg  |

## **Environment**

| Standards                             | CSA C22.2 No 14<br>IEC 61810-1<br>UL 508   |  |
|---------------------------------------|--|--|
| Product Certifications                | CSA<br>CE<br>EAC<br>UL<br>DNV-GL   |  |
| Ambient Air Temperature For Storage   | -4085 °C   |  |
| Ambient Air Temperature For Operation | -4070 °C   |  |
| Ip Degree Of Protection               | IP40   |  |
| Relative Humidity                     | 1085 %   |  |
| Vibration Resistance                  | 3 gn, amplitude = +/- 0.75 mm (f = 10150 Hz)in operation<br>5 gn, amplitude = +/- 0.75 mm (f = 10150 Hz)not in operation |  |

## **Packing Units**

| Unit Type Of Package 1       | PCE     |
|------------------------------|---------|
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 3.45 cm |
| Package 1 Width              | 9.25 cm |
| Package 1 Length             | 8.6 cm  |
| Package 1 Weight             | 228 g   |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

| <b>⊘</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>⊘</b> | Toxic Heavy Metal Free     |     |
| <b>⊘</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |


### **Certifications & Standards**


| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| China Rohs Regulation    | China RoHS declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |


## **RXG12ED**

#### **Dimensions Drawings**

#### **Dimensions**








## **Product datasheet**

## **RXG12ED**

Connections and Schema


## Wiring Diagram



#### Performance Curves

## **Performance Curves**

#### **Maximum Switching Capacity**



X: Switching voltage (V)

Y: Switching current (A)

(1) AC Resistive Load


(2) AC Inductive Load cos(Ø)=0.4

(3) DC Resistive Load

(4) DC Inductive Load (L/R=7ms)

#### Life Expectancy

Resistive Load



X: Contact Current (A)


Y: Operating Cycle Number

#### Life Expectancy

Inductive Load

## **Product datasheet**


## RXG12ED



- X : Contact Current (A)
  Y : Operating Cycle Number
- **NOTE:** These are typical curves, actual durability depends on load, environment, duty cycle, etc.

#### **Coil Operating Range**

#### **DC Coil Operating Range VS Ambient Temperature**



- X : Ambient temperature (°C)
- Y: Coil voltage (U/Uc)
- (1) Permitted operating range area