Product datasheet

Specification





Interface plug-in relay, 10 A, 1 CO, lockable test button, LED, 230 V AC

Local distributor code:

403005796 RXG12P7

EAN Code: 3606480688706

Main

Range Of Product	Harmony Electromechanical Relays	
Series Name	Interface relay	
Product Or Component Type	Plug-in relay	
Device Short Name	RXG	
Contacts Type And Composition	1 C/O	
[Ithe] Conventional Enclosed Thermal Current	10 A at -4055 °C	
Local Signalling	Flag	

Complementary

Status Led	With	
[le] Rated Operational Current	10 A at 30 V (DC) conforming to UL 10 A at 30 V (DC) conforming to IEC 10 A at 250 V (AC) conforming to IEC 10 A at 250 V (AC) conforming to UL	
Electrical Durability	100000 cycles for NO resistive load at 55 °C 100000 cycles for NC resistive load at 55 °C	
Coil Resistance	23500 Ohm +/- 15 %	
Shock Resistance	20 gn in operation 100 gn not in operation	
Mounting Position	Any position	
Average Consumption In Va	0.82 VA 60 Hz	
Control Circuit Voltage Limits	0.81.1 Uc AC	
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz	
Colour Of Cover	Standard	
Drop-Out Voltage Threshold	>= 0.3 Uc AC	
Load Current	10 A at 250 V AC	
Minimum Switching Capacity	500 mW at 100 mA, 5 V DC	
Maximum Switching Capacity	2500 VA	
Control Type	Lockable test button	
Torque Value	0.8 N.m	
Insulation Resistance	1000 MOhm at 500 V DC	
Mechanical Durability	10000000 cycles	
Safety Reliability Data	B10d = 100000	

Overvoltage Category	III	
Maximum Switching Voltage	250 V AC 30 V DC	
Protection Category	RTI	
Operating Rate	<= 1800 cycles/hour under load <= 18000 cycles/hour no-load	
Utilisation Coefficient	20 %	
Pollution Degree	2	
[Ui] Rated Insulation Voltage	250 V conforming to IEC 300 V conforming to CSA 300 V conforming to UL	
Dielectric Strength	1000 V AC between contacts with micro disconnection 5000 V AC between coil and contact with reinforced insulation	
Test Levels	Level A group mounting	
Device Presentation	Complete product	
Contacts Material	Silver alloy (AgSnO2In2O3)	
Net Weight	0.02 kg	

Environment

Standards	IEC 61810-1 CSA C22.2 No 14 UL 508
Product Certifications	CSA EAC UL CE DNV-GL
Ambient Air Temperature For Storage	-4085 °C
Ambient Air Temperature For Operation	-4070 °C
Ip Degree Of Protection	IP40
Relative Humidity	1085 %
Vibration Resistance	3 gn, amplitude = +/- 0.75 mm (f = 10150 Hz)in operation 5 gn, amplitude = +/- 0.75 mm (f = 10150 Hz)not in operation

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.016 cm
Package 1 Width	3.302 cm
Package 1 Length	4.064 cm
Package 1 Weight	18.144 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.5 cm
Package 2 Width	8.2 cm
Package 2 Length	9.1 cm
Package 2 Weight	229 g

Unit Type Of Package 3	S01
Number Of Units In Package 3	200
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	4.81 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations


3 May 2024


RXG12P7

Dimensions Drawings

Dimensions








Product datasheet

RXG12P7

Connections and Schema


Wiring Diagram



Performance Curves

Performance Curves

Maximum Switching Capacity



X: Switching voltage (V)

Y: Switching current (A)

(1) AC Resistive Load


(2) AC Inductive Load cos(Ø)=0.4

(3) DC Resistive Load

(4) DC Inductive Load (L/R=7ms)

Life Expectancy

Resistive Load



X: Contact Current (A)


Y: Operating Cycle Number

Life Expectancy

Inductive Load

Product datasheet


RXG12P7



- X : Contact Current (A)
 Y : Operating Cycle Number
- **NOTE:** These are typical curves, actual durability depends on load, environment, duty cycle, etc.

Coil Operating Range

AC Coil Operating Range VS Ambient Temperature



- X : Ambient temperature (°C)
- Y: Coil voltage (U/Uc)
- (1) Permitted operating range area