Product datasheet

Specification





temperature transmitter - 0..250 °C/32..482 °F - for Universal Pt100 probes

Local distributor code: 387098256

RMPT50BD

EAN Code: 3389110108989

Main

Range Of Product	Harmony Analog
Product Or Component Type	Converter for Universal Pt100 probes
Analogue Input Type	Temperature probe 0250 °C/32482 °F Pt 100 2, 3 or 4 wires
Analogue Output Type	Current 020 mA <= 500 Ohm Current 420 mA <= 500 Ohm Voltage 010 V >= 100 kOhm

Complementary

Reverse polarity protection on output Short-circuit protection on output Reverse polarity protection on power supply Overvoltage protection on output (+/- 30 V)
-1511 V when no input or input wire broken 1115 V when no input or input wire broken
-300 mA when no input or input wire broken 2230 mA when no input or input wire broken
24 V DC non isolated +/- 20 %
<= 40 mA for voltage output <= 60 mA for current output
LED (green) for power ON
+/- 0.5 % of full scale (3 or 4 wires) at 20 °C (temporary performance degradation when subject to electromagnetic interference) +/- 1 % of full scale (2 wires) at 20 °C (temporary performance degradation when subject to electromagnetic interference)
+/- 0.2 % full scale at 20 °C +/- 0.6 % full scale at 60 °C
150 ppm/°C
0.2 Ohm connection in 2 wires
2 x 1.5 mm ² 1 x 2.5 mm ²
0.61.1 N.m
CE
0.5 kV during 1.2/50 μs conforming to IEC 61000-4-5
2000 V
Clip-on (35 mm symmetrical DIN rail) Fixed (mounting plate)
B10d = 30437 MTTFd = 32.9 years
0.12 kg

Environment

Electromagnetic Compatibility	Electrostatic discharge - test level: 6 kV level 3 (contact discharge) conforming to IEC 61000-4-2 Electrostatic discharge - test level: 8 kV level 3 (air discharge) conforming to IEC 61000-4-2
Standards	IEC 60947-1 IEC 60584-1 DIN 43760 IEC 60751
Product Certifications	CSA UL GL
Ip Degree Of Protection	IP20 (terminal block) IP50 (housing)
Fire Resistance	850 °C conforming to IEC 60695-2-1 850 °C conforming to UL
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27
Vibration Resistance	5 gn (f= 10100 Hz) conforming to IEC 60068-2-6
Resistance To Fast Transients	1 kV (on input-output) conforming to IEC 61000-4-4 2 kV (on power supply) conforming to IEC 61000-4-4
Disturbance Radiated/Conducted	CISPR 11 CISPR 22 group 1 - class B
Ambient Air Temperature For Storage	-4085 °C
Ambient Air Temperature For Operation	050 °C mounting side by side 060 °C 2 cm spacing
Pollution Degree	2 conforming to IEC 60664-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	8.2 cm
Package 1 Length	8.5 cm
Package 1 Weight	106.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	47
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.416 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	752
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	98 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


Product datasheet

RMPT50BD

Dimensions Drawings

Analog Interface (Converter)

Dimensions




(1) Terminal block AB1TP435U or AB1RRNTP435U2

RMPT50BD


Mounting and Clearance

Mounting

Mounting on Rails AM1 *****




Panel Mounting



Connections and Schema

Analog Interface: Converter for Universal Pt100 Probe

Wiring Diagram




The input, output and power supply lines must be kept away from the power cables to avoid effects due to induced interference.


The supply, input and output cables must be shielded as indicated in the schemes and must be kept away from each other.

Input Connections


2-wire type



RL1 + RL2 \leq 200 m Ω 3-wire type



RL1 = RL2 = RL3 RL1 + RL2 \geq 200 Ω 4-wire type



RL1 + RL2 ≤ 200 Ω