



Main

Range	Acti 9
Product name	IKQ
Product or component type	Residual current circuit breaker
Poles description	4P
[In] rated current	63 A
Network type	AC
Earth-leakage sensitivity	100 mA

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	400 V AC 50/60 Hz
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	8
Height	81 mm
Width	72 mm
Depth	75 mm
Embedding depth	75 mm
Net weight	0.428 kg
Connections - terminals	Single terminal 35 mm ²

Environment

Standards	BS EN 61008
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------
