Specifications





Interface plug-in relay, 10 A, 1 CO, LED, 220 V AC

RXG13M7

() Discontinued on: 1 Jul 2020

EAN Code: 3606480688805

### Main

Range Of Product	Harmony Relay
Series Name	Interface relay
Product Or Component Type	Plug-in relay
Device Short Name	RXG
Contacts Type And Composition	1 C/O
[Ithe] Conventional Enclosed Thermal Current	10 A at -4055 °C
Local Signalling	Flag

# Complementary

Status Led	With
[Ie] Rated Operational Current	10 A at 30 V (DC) conforming to UL 10 A at 30 V (DC) conforming to IEC 10 A at 250 V (AC) conforming to IEC 10 A at 250 V (AC) conforming to UL
Electrical Durability	100000 cycles for NO resistive load at 55 °C 100000 cycles for NC resistive load at 55 °C
Coil Resistance	21000 Ohm +/- 15 %
Shock Resistance	20 gn in operation 100 gn not in operation
Mounting Position	Any position
Average Consumption In Va	0.82 VA 60 Hz
Control Circuit Voltage Limits	0.81.1 Uc AC
[Uc] Control Circuit Voltage	220 V AC 50/60 Hz
Colour Of Cover	Standard
Drop-Out Voltage Threshold	>= 0.3 Uc AC
Load Current	10 A at 250 V AC
Minimum Switching Capacity	500 mW at 100 mA, 5 V DC
Maximum Switching Capacity	2500 VA
Torque Value	0.8 N.m
Contact Resistance	100 mOhm
Insulation Resistance	1000 MOhm at 500 V DC
Electrical Insulation Class	Class F

Mechanical Durability	1000000 cycles
Safety Reliability Data	B10d = 100000
Operating Time	20 ms
Reset Time	20 ms
Overvoltage Category	III
Maximum Switching Voltage	250 V AC 30 V DC
Protection Category	RT I
Operating Rate	<= 1800 cycles/hour under load <= 18000 cycles/hour no-load
Pollution Degree	2
Utilisation Coefficient	20 %
[Ui] Rated Insulation Voltage	250 V conforming to IEC 300 V conforming to CSA 300 V conforming to UL
Dielectric Strength	1000 V AC between contacts with micro disconnection 5000 V AC between coil and contact with reinforced insulation
Test Levels	Level A group mounting
Device Presentation	Complete product
Contacts Material	Silver alloy (AgSnO2In2O3)
Net Weight	0.02 kg

# Environment

Standards	IEC 61810-1	
	UL 508	
	CSA C22.2 No 14	
Product Certifications	CE	
	EAC	
	CSA	
	UL	
	DNV-GL	
Ambient Air Temperature For Storage	-4085 °C	
Ambient Air Temperature For Operation	-4070 °C	
Ip Degree Of Protection	IP40	
Relative Humidity	1085 %	
Vibration Resistance	3 gn, amplitude = +/- 0.75 mm (f = 10150 Hz)in operation	
	5 gn, amplitude = +/- 0.75 mm (f = 10150 Hz)not in operation	

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

# Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

13(MAX) 0.51(MAX)


**Dimensions Drawings** 

#### Dimensions



Connections and Schema


#### Wiring Diagram



#### Performance Curves

#### Performance Curves

#### **Maximum Switching Capacity**




X : Switching voltage (V)

- Y: Switching current (A)
- (1) AC Resistive Load
- (2) AC Inductive Load cos(Ø)=0.4
- (3) DC Resistive Load
- (4) DC Inductive Load (L/R=7ms)

#### Life Expectancy

Resistive Load




X : Contact Current (A)

#### $\mathbf{Y}:$ Operating Cycle Number

#### Life Expectancy

Inductive Load




X : Contact Current (A)

Y: Operating Cycle Number

**NOTE:** These are typical curves, actual durability depends on load, environment, duty cycle, etc.

#### Coil Operating Range

#### AC Coil Operating Range VS Ambient Temperature



X : Ambient temperature (°C)

Y: Coil voltage (U/Uc)

(1) Permitted operating range area