# **Product datasheet**

Specification





# compact smart relay Zelio Logic - 10 I O - 24 V DC - no clock - no display

Local distributor code: 389838265

SR2D101BD

EAN Code: 3389110549751

#### Main

Range Of Product	Zelio Logic
Product Or Component Type	Compact smart relay

## Complementary

Without
240 with ladder programming
690 ms
10 years at 25 °C
12 min/year at 055 °C 6 s/month at 25 °C
Program memory on each power up
24 V DC
19.230 V
100 mA (without extension)
3 W without extension
With
6 conforming to IEC 61131-2 Type 1
Resistive
24 V DC
4 mA
1 kHz for discrete input
>= 15 V for I1IA and IHIR discrete input circuit >= 15 V for IBIG used as discrete input circuit
<= 5 V for I1IA and IHIR discrete input circuit <= 5 V for IBIG used as discrete input circuit
>= 1.2 mA (IBIG used as discrete input circuit) >= 2.2 mA (I1IA and IHIR discrete input circuit)
<= 0.5 mA (IBIG used as discrete input circuit) <= 0.75 mA (I1IA and IHIR discrete input circuit)
3-wire proximity sensors PNP for discrete input
0
12 kOhm for IBIG used as analogue input circuit 12 kOhm for IBIG used as discrete input circuit 7.4 kOhm for I1IA and IHIR discrete input circuit
4 relay

Output Voltage Limits	24250 V AC (relay output) 530 V DC (relay output)
Contacts Type And Composition	NO for relay output
Output Thermal Current	8 A for all 4 outputs for relay output
Electrical Durability	AC-12: 500000 cycles at 230 V, 1.5 A for relay output conforming to IEC 60947-5-1 AC-15: 500000 cycles at 230 V, 0.9 A for relay output conforming to IEC 60947-5-1 DC-12: 500000 cycles at 24 V, 1.5 A for relay output conforming to IEC 60947-5-1 DC-13: 500000 cycles at 24 V, 0.6 A for relay output conforming to IEC 60947-5-1
Switching Capacity In Ma	>= 10 mA at 12 V (relay output)
Operating Rate In Hz	0.1 Hz (at le) for relay output 10 Hz (no load) for relay output
Mechanical Durability	10000000 cycles for relay output
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1 and EN/IEC 60664-1
Clock	Without
Response Time	10 ms (from state 0 to state 1) for relay output 5 ms (from state 1 to state 0) for relay output
Connections - Terminals	Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) semi-solid Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) solid Screw terminals, 1 x 0.251 x 2.5 mm² (AWG 24AWG 14) flexible with cable end Screw terminals, 2 x 0.22 x 1.5 mm² (AWG 24AWG 16) solid Screw terminals, 2 x 0.252 x 0.75 mm² (AWG 24AWG 18) flexible with cable end
Tightening Torque	0.5 N.m
Overvoltage Category	III conforming to IEC 60664-1
Net Weight	0.22 kg

### **Environment**

Livironnient		
Immunity To Microbreaks	1 ms	
Product Certifications	CSA	
	UL	
	GL	
	GOST	
	C-Tick	
Standards	IEC 61000-4-5	
	IEC 61000-4-12	
	IEC 60068-2-27 Ea	
	IEC 61000-4-2 level 3	
	IEC 60068-2-6 Fc	
	IEC 61000-4-11	
	IEC 61000-4-4 level 3	
	IEC 61000-4-6 level 3	
	IEC 61000-4-3	
Ip Degree Of Protection	IP20 (terminal block) conforming to IEC 60529	
	IP40 (front panel) conforming to IEC 60529	
Environmental Characteristic	EMC directive conforming to IEC 61000-6-2	
	EMC directive conforming to IEC 61000-6-3	
	EMC directive conforming to IEC 61000-6-4	
	EMC directive conforming to IEC 61131-2 zone B	
	Low voltage directive conforming to IEC 61131-2	
Disturbance Radiated/Conducted	Class B conforming to EN 55022-11 group 1	
Pollution Degree	2 conforming to IEC 61131-2	
Ambient Air Temperature For	-2040 °C in non-ventilated enclosure conforming to IEC 60068-2-1 and IEC	
Operation	60068-2-2	
	-2055 °C conforming to IEC 60068-2-1 and IEC 60068-2-2	
Ambient Air Temperature For Storage	-4070 °C	
Operating Altitude	2000 m	

Maximum Altitude Transport	3048 m
Relative Humidity	95 % without condensation or dripping water

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.9 cm
Package 1 Width	9.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	199.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.456 kg

## **Contractual warranty**

4 May 2024

Warranty 18 months

## Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**


Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

4 May 2024

#### **Dimensions Drawings**


#### **Compact and Modular Smart Relays**

#### Mounting on 35 mm/1.38 in. DIN Rail




#### (1) With SR2USB01 or SR2BTC01

#### Screw Fixing (Retractable Lugs)



#### (1) With SR2USB01 or SR2BTC01


#### **Position of Display**



#### Connections and Schema


#### **Compact and Modular Smart Relays**

#### Connection of Smart Relays on DC Supply



- (1) 1 A quick-blow fuse or circuit-breaker.
- (2) Fuse or circuit-breaker.
- (3) Inductive load.
- (4) Q9 and QA: 5 A (max. current in terminal C: 10 A).

#### **Discrete Input Used for 3-Wire Sensors**



(1) 1 A quick-blow fuse or circuit-breaker.


#### SR2D101BD

#### Performance Curves

#### **Compact and Modular Smart Relays**

#### **Electrical Durability of Relay Outputs**

(in millions of operating cycles, conforming to IEC/EN 60947-5-1) DC-12 (1)




X: Current (A)

Y: Millions of operating cycles

(1) DC-12: control of resistive loads and of solid state loads isolated by opto-coupler, L/R ≤ 1 ms.

DC-13 (1)



X: Current (A)

Y: Millions of operating cycles

(1) DC-13: switching electromagnets,  $L/R \le 2 \times (Ue \times Ie)$  in ms, Ue: rated operational voltage, Ie: rated operational current (with a protection diode on the load, DC-12 curves must be used with a coefficient of 0.9 applied to the number in millions of operating cycles).