Product datasheet

Specification





Miniature plug-in relay, 10 A, 3 CO, 230 V AC

Local distributor code: 389837583

RXM3AB1P7

EAN Code: 3389119403610

Main

Range Of Product	Harmony Electromechanical Relays	
Series Name	Miniature	
Product Or Component Type	Plug-in relay	
Device Short Name	RXM	
Contacts Type And Composition	3 C/O	
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz	
Status Led	Without	
Control Type	Lockable test button	
Utilisation Coefficient	20 %	

Complementary

Flat
250 V conforming to IEC 300 V conforming to CSA 300 V conforming to UL
4 kV during 1.2/50 μs
AgNi
10 A at 28 V (DC) NO conforming to IEC 10 A at 250 V (AC) NO conforming to IEC 5 A at 28 V (DC) NC conforming to IEC 5 A at 250 V (AC) NC conforming to IEC 10 A at 30 V (DC) conforming to UL 10 A at 277 V (AC) conforming to UL
6.7 A
250 V conforming to IEC
10 A at 250 V AC 10 A at 28 V DC
2500 VA/280 W
170 mW at 10 mA, 17 V
<= 1200 cycles/hour under load <= 18000 cycles/hour no-load
10000000 cycles
100000 cycles for resistive load
1.2 at 60 Hz
1.2 VA at 60 Hz

Drop-Out Voltage Threshold	>= 0.15 Uc
Operate Time	20 ms
Release Time	20 ms
Average Coil Resistance	15000 Ohm at 20 °C +/- 15 %
Rated Operational Voltage Limits	184253 V AC
Safety Reliability Data	B10d = 100000
Protection Category	RTI
Test Levels	Level A group mounting
Operating Position	Any position
Cad Overall Height	82.8 mm
Cad Overall Depth	80.35 mm
Net Weight	0.037 kg
Device Presentation	Complete product

Environment

Dielectric Strength	1300 V AC between contacts with micro disconnection
	2000 V AC between coil and contact
	2000 V AC between poles
Product Certifications	UL
	Lloyd's
	CE
	CSA
	GOST
	IECEE CB Scheme
Standards	IEC 61810-1
	CSA C22.2 No 14
	UL 508
Ambient Air Temperature For Storage	-4085 °C
Ambient Air Temperature For Operation	-4055 °C
Vibration Resistance	3 gn, amplitude = +/- 1 mm (f = 10150 Hz)5 cycles in operation
	5 gn, amplitude = +/- 1 mm (f = 10150 Hz)5 cycles not operating
Ip Degree Of Protection	IP40 conforming to IEC 60529
Shock Resistance	10 gn for in operation
	30 gn for not operating
Pollution Degree	2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.200 cm
Package 1 Width	2.700 cm
Package 1 Length	4.800 cm
Package 1 Weight	36.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.100 cm

Package 2 Width	10.300 cm
Package 2 Length	12.600 cm
Package 2 Weight	388.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	240
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	9.801 kg

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


19 Apr 2024

Dimensions Drawings

Dimensions




Pin Side View




RXM3AB1P7

Connections and Schema

Wiring Diagram






Symbols shown in blue correspond to Nema marking.

Performance Curves

Electrical Durability of Contacts

Durability (inductive load) = durability (resistive load) x reduction coefficient. Resistive AC load



X Switching capacity (kVA)

Y Durability (Number of operating cycles)


A RXM2AB...

B RXM3AB***

C RXM4AB•••


D RXM4GB***

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

A RXM2AB***

Product datasheet

RXM3AB1P7

B RXM3AB***

C RXM4AB***


D RXM4GB***

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

For inductive load, to increase relay life cycles, please add a proper load protection circuit (eg: RC protection/Varistor/free Wheeling diode -DC load only-).

For low level loads (below 10mA), we recommend to use RXM*GB series with bifurcated contacts relays instead.

AC Coil Voltage and Operating Temperature under continuous duty



X : Operating temperature (°C)Y : AC coil voltage (UC)