# **Product datasheet**

Specification





## discrete I/O extension module - 6 I O - 24 V AC - for Zelio Logic

Local distributor code:

389838414 SR3XT61B

EAN Code: 3389110550177

① To be discontinued

## Main

Range Of Product	Zelio Logic
Product Or Component Type	Discrete I/O extension module

## Complementary

J		
Number Or Control Scheme Lines	120 with ladder programming	
Cycle Time	690 ms	
Backup Time	10 years at 25 °C	
Clock Drift	12 min/year at 055 °C	
Checks	Program memory on each power up	
[Us] Rated Supply Voltage	24 V AC	
Supply Voltage Limits	20.428.8 V	
Supply Frequency	50/60 Hz	
Reverse Polarity Protection	With	
Discrete Input Number	4	
Discrete Input Voltage	24 V AC	
Discrete Input Current	4.4 mA	
Discrete Input Frequency	4753 Hz 5763 Hz	
Voltage State 1 Guaranteed	>= 14 V for discrete input	
Voltage State 0 Guaranteed	<= 5 V for discrete input	
Current State 1 Guaranteed	>= 2 mA (discrete input)	
Current State 0 Guaranteed	<= 0.5 mA (discrete input)	
Input Impedance	4.6 kOhm for discrete input	
Number Of Outputs	2 relay	
Output Voltage Limits	530 V DC (relay output) 24250 V AC	
Contacts Type And Composition	NO for relay output	
Output Thermal Current	8 A for all 2 outputs for relay output	
Electrical Durability	AC-15: 500000 cycles at 230 V, 0.9 A for relay output conforming to IEC 60947-5-1 AC-12: 500000 cycles at 230 V, 1.5 A for relay output conforming to IEC 60947-5-1 DC-13: 500000 cycles at 24 V, 0.6 A for relay output conforming to IEC 60947-5-1 DC-12: 500000 cycles at 24 V, 1.5 A for relay output conforming to IEC 60947-5-1	
Switching Capacity In Ma	>= 10 mA at 12 V (relay output)	

Operating Rate In Hz	0.1 Hz (at le) for relay output 10 Hz (no load) for relay output	
Mechanical Durability	10000000 cycles for relay output	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1 and EN/IEC 60664-1	
Response Time	50 ms with ladder programming (from state 0 to state 1) for discrete input 50 ms with ladder programming (from state 1 to state 0) for discrete input 50255 ms with FBD programming (from state 0 to state 1) for discrete input 50255 ms with FBD programming (from state 1 to state 0) for discrete input 10 ms (from state 0 to state 1) for relay output 5 ms (from state 1 to state 0) for relay output	
Connections - Terminals	Screw terminals, 1 x 0.251 x 2.5 mm² (AWG 24AWG 14) flexible with cable end Screw terminals, 2 x 0.252 x 0.75 mm² (AWG 24AWG 18) flexible with cable end Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) semi-solid Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) solid Screw terminals, 2 x 0.22 x 1.5 mm² (AWG 24AWG 16) solid	
Tightening Torque	0.5 N.m	
Overvoltage Category	III conforming to IEC 60664-1	
Net Weight	0.125 kg	
Environment		
Product Certifications	CSA GL GOST UL C-Tick	
Standards	IEC 61000-4-12 IEC 61000-4-6 level 3 IEC 61000-4-3 IEC 60068-2-27 Ea IEC 61000-4-11 IEC 61000-4-5 IEC 61000-4-5 IEC 60068-2-6 Fc	
Ip Degree Of Protection	IP20 (terminal block) conforming to IEC 60529 IP40 (front panel) conforming to IEC 60529	
Environmental Characteristic	EMC directive conforming to IEC 61000-6-2 EMC directive conforming to IEC 61000-6-3 EMC directive conforming to IEC 61000-6-4 EMC directive conforming to IEC 61131-2 zone B Low voltage directive conforming to IEC 61131-2	
Disturbance Radiated/Conducted	Class B conforming to EN 55022-11 group 1	
Pollution Degree	2 conforming to IEC 61131-2	
Ambient Air Temperature For Operation	-2040 °C in non-ventilated enclosure conforming to IEC 60068-2-1 and IEC 60068-2-2 -2055 °C conforming to IEC 60068-2-1 and IEC 60068-2-2	
Ambient Air Temperature For Storage	-4070 °C	
Operating Altitude	2000 m	
Maximum Altitude Transport	3048 m	
Relative Humidity	95 % without condensation or dripping water	
Packing Units		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	6.000 cm	

Package 1 Width	11.000 cm
Package 1 Length	6.500 cm
Package 1 Weight	117.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	48
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.050 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

### **Certifications & Standards**


Circularity Profile	End of Life Information	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
<b>Environmental Disclosure</b>	Product Environmental Profile	
China Rohs Regulation	China RoHS declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
Reach Regulation	REACh Declaration	

## SR3XT61B


## **Dimensions Drawings**

### I/O Extension Modules

### Mounting on 35 mm/1.38 in. DIN Rail



### Screw Fixing (Retractable Lugs)




SR3	a (mm/in.)	G (mm/in.)
XT61••	35 / 1.38	25 / 0.98
XT101••	72 / 2.83	60 / 2.36
XT141••	72 / 2.83	60 / 2.36

#### Connections and Schema

#### **Connection of Smart Relays on AC Supply**


#### SR --- 1B, SR --- 1FU



- (1) 1 A quick-blow fuse or circuit-breaker.
- (2) Fuse or circuit-breaker.
- (3) Inductive load.
- (4) Q9 and QA: 5 A (max. current in terminal C: 10 A).

#### With Discrete I/O Extension Module

SR3B•••B + SR3XT•••B, SR3B•••FU + SR3XT•••FU



(1) 1 A quick-blow fuse or circuit-breaker.


NOTE: QF and QG: 5 A for SR3XT141..

#### Performance Curves

#### **Compact and Modular Smart Relays**

#### **Electrical Durability of Relay Outputs**


(in millions of operating cycles, conforming to IEC/EN 60947-5-1) AC-12 (1)



X: Current (A)

Y: Millions of operating cycles


(1) AC-12: switching resistive loads and opto-coupler isolated solid-state loads, cos ≥ 0.9. AC-14 (1)



X: Current (A)

Y: Millions of operating cycles

(1) AC-14: switching small electromagnetic loads ≤ 72 VA, make: cos = 0.3, break: cos = 0.3. AC-15 (1)



X: Current (A)

Y: Millions of operating cycles

(1) AC-15: switching electromagnetic loads ≥ 72 VA, make: cos = 0.7, break: cos = 0.4.