



# controller M241 40 IO transistor NPN Ethernet

TM241CE40U

EAN Code: 3606480611162

#### Main

Range Of Product	Modicon M241	
Product Or Component Type	Logic controller	
[Us] Rated Supply Voltage	24 V DC	
Discrete Input Number	24, discrete input 8 fast input conforming to IEC 61131-2 Type 1	
Discrete Output Type	Transistor	
Discrete Output Number	16 transistor 4 fast output	
Discrete Output Voltage	24 V DC for transistor output	
Discrete Output Current	0.1 A for fast output (PTO mode) (Q0Q3) 0.5 A for transistor output (Q0Q15)	

## Complementary

Discrete I/O Number	40
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)
Supply Voltage Limits	20.428.8 V
Inrush Current	50 A
Power Consumption In W	32.640.4 W (with max number of I/O expansion module)
Discrete Input Logic	Sink or source
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Voltage State 1 Guaranteed	>= 15 V for input
Voltage State 0 Guaranteed	<= 5 V for input
Discrete Input Current	10.7 mA for fast input 7 mA for input
Input Impedance	4.7 kOhm for input 2.81 kOhm for fast input
Response Time	<= 2 μs turn-on, I0I7 terminal(s) for fast input <= 2 μs turn-off, I0I7 terminal(s) for fast input <= 2 μs turn-on, Q0Q3 terminal(s) for fast output <= 2 μs turn-off, Q0Q3 terminal(s) for fast output 50 μs turn-on, I0I15 terminal(s) for input 50 μs turn-off, I0I15 terminal(s) for input <= 34 μs turn-on, Q0Q15 terminal(s) for output

<= 250 µs turn-off, Q0...Q15 terminal(s) for output

Configurable Filtering Time	1 µs for fast input
	12 ms for fast input
	0 ms for input 1 ms for input
	4 ms for input
	12 ms for input
Discrete Output Logic	Negative logic (sink)
Output Voltage Limits	30 V DC
Maximum Current Per Output Common	2 A
Maximum Output Frequency	20 kHz for fast output (PWM mode)
	100 kHz for fast output (PLS mode) 1 kHz for output
Accuracy	+/- 0.1 % at 0.020.1 kHz for fast output +/- 1 % at 0.11 kHz for fast output
Maximum Leakage Current	5 μA for output
Maximum Voltage Drop	<1 V
Maximum Tungsten Load	<2.4 W
Protection Type	Short-circuit protection
	Short-circuit and overload protection with automatic reset
	Reverse polarity protection for fast output
Reset Time	10 ms automatic reset output 12 s automatic reset fast output
Memory Capacity	64 MB for system memory RAM
Data Backed Up	128 MB built-in flash memory for backup of user programs
Data Storage Equipment	<= 16 GB SD card (optional)
Battery Type	BR2032 lithium non-rechargeable, battery life: 4 year(s)
Backup Time	2 years at 25 °C
<b>Execution Time For 1 Kinstruction</b>	0.3 ms for event and periodic task 0.7 ms for other instruction
Application Structure	8 external event tasks
	3 cyclic master tasks + 1 freewheeling task
	4 cyclic master tasks
	8 event tasks
Realtime Clock	With
Clock Drift	<= 60 s/month at 25 °C
Positioning Functions	PTO function 4 channel(s) (positioning frequency: 100 kHz) PTO function 4 channel(s) for transistor output (positioning frequency: 1 kHz)
Counting Input Number	4 fast input (HSC mode) at 200 kHz 16 standard input at 1 kHz
Control Signal Type	A/B at 100 kHz for fast input (HSC mode)
	Pulse/direction at 200 kHz for fast input (HSC mode) Single phase at 200 kHz for fast input (HSC mode)
Integrated Connection Type	Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface
	Non isolated serial link serial 2 with removable screw terminal block connector and
	RS485 interface
	USB port with mini B USB 2.0 connector Ethernet with RJ45 connector
Cumplu	
Supply ———————————————————————————————————	(serial 1)serial link supply: 5 V, <200 mA
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485
	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for bus length of 3 m for USB
	10/100 Mbit/s for Ethernet
Communication Port Protocol	Non isolated serial link: Modbus master/slave

Port Ethernet	10BASE-T/100BASE-TX - 1 port(s) copper cable
Ethernet Services	FDR DHCP server via TM4 Ethernet switch network module DHCP client embedded Ethernet port
	SMS notifications
	Updating firmware
	SNMP client/server
	Programming
	NGVL
	Monitoring
	IEC VAR ACCESS
	FTP client/server
	Downloading SQL client
	Modbus TCP client I/O scanner
	Ethernet/IP originator I/O scanner embedded Ethernet port
	Ethernet/IP target, Modbus TCP server and Modbus TCP slave
	Send and receive email from the controller based on TCP/UDP library
	Web server (WebVisu & XWeb system)
	OPC UA server
	DNS client
Local Signalling	1 LED (green) for PWR
	1 LED (green) for RUN
	1 LED (red) for module error (ERR)
	1 LED (red) for I/O error (I/O)
	1 LED (green) for SD card access (SD)
	1 LED (red) for BAT
	1 LED (green) for SL1 1 LED (green) for SL2
	1 LED (green) for St.2  1 LED (red) for bus fault on TM4 (TM4)
	1 LED per channel (green) for I/O state
	1 LED (green) for Ethernet port activity
Electrical Connection	removable screw terminal blockfor inputs and outputs (pitch 5.08 mm)
	removable screw terminal blockfor connecting the 24 V DC power supply (pitch 5.08
	mm)
	·
Maximum Cable Distance	Unshielded cable: <50 m for input
Between Devices	Shielded cable: <10 m for fast input
	Unshielded cable: <50 m for output
	Shielded cable: <3 m for fast output
Insulation	Between supply and internal logic at 500 V AC
	Non-insulated between supply and ground
	Between input and internal logic at 500 V AC
	Non-insulated between inputs
	Between fast input and internal logic at 500 V AC
	Between output and internal logic at 500 V AC
	Non-insulated between outputs  Between fast output and internal logic at 500 V AC
	Between output groups at 500 V AC
A4	
Marking	CE
Surge Withstand	1 kV power lines (DC) common mode conforming to IEC 61000-4-5
	1 kV shielded cable common mode conforming to IEC 61000-4-5
	0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5
	1 kV relay output differential mode conforming to IEC 61000-4-5
	1 kV input common mode conforming to IEC 61000-4-5  1 kV transistor output common mode conforming to IEC 61000-4-5
	1 kV transistor output common mode comonning to IEO 01000-4-3
Web Services	Web server
Maximum Number Of	8 Modbus server
Connections	8 SoMachine protocol
	10 web server
	4 FTP server
	16 Ethernet/IP target 8 Modbus client
Number Of Server Device(S)	64 Modhus TCD
boi oi oeivei bevice(o)	64 Modbus TCP: 16 EtherNet/IP:
Cycle Time	10 mg 46 EthorNot/ID
	10 ms 16 EtherNet/IP 64 ms 64 Modbus TCP

Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
Height	90 mm	
	95 mm	
Width	190 mm	
Net Weight	0.62 kg	
Environment		
Standards	ANSI/ISA 12-12-01	
	CSA C22.2 No 142	
	CSA C22.2 No 213	

Environment	
Standards	ANSI/ISA 12-12-01 CSA C22.2 No 142 CSA C22.2 No 213 IEC 61131-2:2007 Marine specification (LR, ABS, DNV, GL) UL 508
Product Certifications	RCM cULus CE UKCA DNV-GL ABS LR
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2
Resistance To Electromagnetic Fields	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3
Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4 1 kV (Ethernet line) conforming to IEC 61000-4-4 1 kV (serial link) conforming to IEC 61000-4-4 1 kV (input) conforming to IEC 61000-4-4 1 kV (transistor output) conforming to IEC 61000-4-4
Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL) 10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)
Electromagnetic Emission	Conducted emissions - test level: 12069 dBμV/m QP ( power lines) at 10150 kHz conforming to IEC 55011 Conducted emissions - test level: 63 dBμV/m QP ( power lines) at 1.530 MHz conforming to IEC 55011 Radiated emissions - test level: 40 dBμV/m QP class A at 30230 MHz conforming to IEC 55011 Conducted emissions - test level: 7963 dBμV/m QP ( power lines) at 1501500 kHz conforming to IEC 55011 Radiated emissions - test level: 47 dBμV/m QP class A at 2301000 MHz conforming to IEC 55011
Immunity To Microbreaks	10 ms
Ambient Air Temperature For Operation	-1050 °C (vertical installation) -1055 °C (horizontal installation)
Ambient Air Temperature For Storage	-2570 °C
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)
Ip Degree Of Protection	IP20 with protective cover in place
Pollution Degree	2
Operating Altitude	02000 m
Storage Altitude	03000 m

Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail 3 gn at 8.4150 Hz on symmetrical rail 3.5 mm at 58.4 Hz on panel mounting 3 gn at 8.4150 Hz on panel mounting	
Shock Resistance	15 gn for 11 ms	

## **Packing Units**

PCE
1
11.415 cm
13.024 cm
22.936 cm
770.0 g
S03
6
30 cm
30 cm
40 cm
5.49 kg
P06
48
75.0 cm
40.0 cm
80.0 cm
54 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**


Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Environmental Disclosure</b>	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration


## **Product datasheet**

## **TM241CE40U**

## **Dimensions Drawings**

#### **Dimensions**







## **Product datasheet**

## **TM241CE40U**


Mounting and Clearance

#### Clearance






#### **Mounting Position**




#### **Acceptable Mounting**




**NOTE:** Expansion modules must be mounted above the logic controller.

#### **Incorrect Mounting**



#### **Direct Mounting On a Panel Surface**

#### **Mounting Hole Layout**




#### **TM241CE40U**

#### Connections and Schema

#### **Digital Inputs**

#### Wiring Diagram



(\*): Type T fuse

(1): The COM0, COM1 and COM2 terminals are not connected internally

(A): Sink wiring (positive logic)


(B): Source wiring (negative logic)

#### Fast Input Wiring (I0...I7)



#### **Fast Transistor Outputs**


#### Wiring Diagram



- (\*): Type T fuse
- (1) The V0+, V1+, V2+ and V3+ terminals are not connected internally.
- (2) The V0-, V1-, V2- and V3- terminals are not connected internally.


#### **Transistor Outputs**

#### Wiring Diagram



- (\*): Type T fuse
- (1): The V1+, V2+ and V3+ terminals are not connected internally.
- (2): The V1-, V2- and V3- terminals are not connected internally.

#### **USB Mini-B Connection**



#### **Ethernet Connection to a PC**

