Product datasheet

Specifications





Modicon TM3 - 2 analog inputs high resolution (spring) 24Vdc

TM3AI2HG

EAN Code: 3606480648892

Main

Range Of Product	Modicon TM3	
Product Or Component Type	Analog input module	
Range Compatibility	Modicon M221	
	Modicon M241	
	Modicon M251	
	Modicon M262	
Analogue Input Number	2	
Analogue Input Type	current 420 mA	
	current 020 mA	
	voltage 010 V	
	voltage - 1010 V	

Complementary

Analogue Input Resolution	16 bits 15 bits + sign	
Permissible Continuous Overload	13 V, analogue input type: voltage 40 mA, analogue input type: current	
Input Impedance	<= 50 Ohm current >= 1 MOhm voltage	
Lsb Value	2.44 mV 010 Vvoltage 4.88 mV - 1010 Vvoltage 4.88 μA 020 mAcurrent 3.91 μA 420 mAcurrent	
Conversion Time	1 ms + 1 ms per channel + 1 controller cycle time	
Sampling Duration	1 ms	
Absolute Accuracy Error	+/- 0.1 % of full scale at 25 °C +/- 1 % of full scale	
Temperature Drift	+/- 0.006 %FS/°C	
Repeat Accuracy	+/-0.5 %FS	
Non-Linearity	+/- 0.01 %FS	
Cross Talk	<= 1 LSB	
[Us] Rated Supply Voltage	24 V DC	
Supply Voltage Limits	20.428.8 V	
Type Of Cable	Twisted shielded pairs cable <30 m for input circuit	
Current Consumption	30 mA at 5 V DC via bus connector no load 40 mA at 5 V DC via bus connector full load 25 mA at 24 V DC via external supply	
Local Signalling	1 LED (green) for PWR	

Electrical Connection	11 x 2.5 mm ² removable spring terminal block with pitch 5.08 mm adjustment for inputs and supply	
Insulation Between input and supply at 1500 V AC Between input and internal logic at 500 V AC		
Marking	CE	
Surge Withstand	1 kV power supply common mode conforming to IEC 61000-4-5 0.5 kV power supply differential mode conforming to IEC 61000-4-5 1 kV input common mode conforming to IEC 61000-4-5	
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
Height	90 mm	
Depth	70 mm	
Width	23.6 mm	
Net Weight	0.1 kg	

Environment

Standards	IEC 61131-2	
Product Certifications	CE UKCA RCM EAC cULus cULus HazLoc	
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2	
Resistance To Electromagnetic Fields	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3	
Resistance To Magnetic Fields	30 A/m conforming to IEC 61000-4-8	
Resistance To Fast Transients	1 kV (I/O) conforming to IEC 61000-4-4	
Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)	
Electromagnetic Emission	Radiated emissions - test level: 40 dBµV/m QP class A (10 m) at 30230 MHz conforming to IEC 55011 Radiated emissions - test level: 47 dBµV/m QP class A (10 m) at 2301000 MHz conforming to IEC 55011	
Immunity To Microbreaks	10 ms	
Ambient Air Temperature For Operation	-1055 °C horizontal installation -1035 °C vertical installation	
Ambient Air Temperature For Storage	-2570 °C	
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)	
Ip Degree Of Protection	IP20	
Pollution Degree	2	
Operating Altitude	02000 m	
Storage Altitude	03000 m	
Vibration Resistance	3.5 mm at 5…8.4 Hz on DIN rail 3 gn at 8.4…150 Hz on DIN rail	
Shock Resistance	15 gn for 11 ms	

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	10.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	200.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.246 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings


Dimensions




(*) 8.5 mm/0.33 in when the clamp is pulled out.

Mounting and Clearance

Spacing Requirements




Mounting on a Rail




Incorrect Mounting





(1) Install a mounting strip


Mounting Hole Layout



Connections and Schema

Analogue Input Module

Wiring Diagram (Current / Voltage)



- (*) Type T fuse
- (1) Current/Voltage analog output device