



Modicon TM3 - 16 outputs transistor NPN (spring)

TM3DQ16UG

EAN Code: 3606480611599

Main

Range Of Product	Modicon TM3	
Product Or Component Type	Discrete output module	
Range Compatibility	Modicon M241	
	Modicon M251	
	Modicon M221	
	Modicon M262	
Discrete Output Type	Transistor	
Discrete Output Number	16	
Discrete Output Logic	Negative logic (sink)	
Discrete Output Voltage	24 V DC for transistor output	
Discrete Output Current	300 mA for transistor output	

Complementary

Discrete I/O Number	16
Current Consumption	5 mA at 5 V DC via bus connector (at state off) 0 mA at 24 V DC via bus connector (at state off) 15 mA at 5 V DC via bus connector (at state on) 20 mA at 24 V DC via bus connector (at state on)
Response Time	450 μs (turn-on) 450 μs (turn-off)
Maximum Leakage Current	0.1 mA for transistor output
Maximum Voltage Drop	<0.4 V
Local Signalling	1 LED per channel (green) for output status
Electrical Connection	10 x 1.5 mm² removable screw terminal block with pitch 3.81 mm adjustment for outputs 10 x 1.5 mm² removable spring terminal block with pitch 3.81 mm adjustment for outputs
Maximum Cable Distance Between Devices	Unshielded cable: <30 m for transistor output
Insulation	Between output and internal logic at 500 V AC Non-insulated between outputs
Marking	CE
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit
Height	90 mm
Depth	81.3 mm
Width	21.4 mm

Net Weight 0.76 kg

Environment

Standards	IEC 61131-2
Product Certifications	cULus
	CE
	UKCA
	RCM
	EAC
	cULus HazLoc
Resistance To Electrostatic	8 kV in air conforming to IEC 61000-4-2
Discharge	4 kV on contact conforming to IEC 61000-4-2
Resistance To Electromagnetic	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3
Fields	3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3
	1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8
Resistance To Fast Transients	1 kV for I/O conforming to IEC 61000-4-4
Surge Withstand	1 kV I/O common mode conforming to IEC 61000-4-5 DC
Resistance To Conducted	10 V 0.1580 MHz conforming to IEC 61000-4-6
Disturbances	3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to
	Marine specification (LR, ABS, DNV, GL)
Electromagnetic Emission	Radiated emissions - test level: 40 dBµV/m QP class A (10 m) at 30230 MHz
	conforming to IEC 55011
	Radiated emissions - test level: 47 dBµV/m QP class A (10 m) at 2301000 MHz
	conforming to IEC 55011
Ambient Air Temperature For	-1035 °C vertical installation
Operation	-1055 °C horizontal installation
Ambient Air Temperature For	-2570 °C
Storage Relative Humidity	10. OF 9/ without condensation (in apprehim)
Neiative Humaity	1095 %, without condensation (in operation)
	1095 %, without condensation (in storage)
lp Degree Of Protection	IP20 with protective cover in place
Pollution Degree	2
Operating Altitude	02000 m
Storage Altitude	03000 m
Vibration Resistance	3.5 mm at 58.4 Hz on DIN rail
	3 gn at 8.4150 Hz on DIN rail
	3.5 mm at 58.4 Hz on panel
	3 gn at 8.4150 Hz on panel
Shock Resistance	15 gn for 11 ms

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	10.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	245.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15 cm

Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.244 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	80 cm
Package 3 Width	105 cm
Package 3 Length	125 cm
Package 3 Weight	85.48 kg

Logistical informations

Country Of Origin US

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


②	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions




(*) 8.5 mm/0.33 in. when the clamp is pulled out.


Product datasheet

TM3DQ16UG


Mounting and Clearance

Spacing Requirements







Mounting on a Rail



Incorrect Mounting




Mounting on a Panel Surface



(1) Install a mounting strip

Mounting Hole Layout




Product datasheet

TM3DQ16UG

Connections and Schema

Digital Transistor Output Module (16-channel, Sink)

Wiring Diagram



- (*) Type T Fuse
- (**) Type F Fuse