


Product datasheet


Specifications



memory cartridge - for smart relay Zelio Logic firmware - up to v 2.4 - EEPROM

Local distributor code:
389537896

SR2MEM01

 **Discontinued on:** 7 Aug 2023

 **Discontinued**

EAN Code: 3389110550306

Main

Range Of Product	Zelio Logic
Accessory / Separate Part Designation	EEPROM memory cartridge
Accessory / Separate Part Type	Memory cartridge
Accessory / Separate Part Category	Separate parts
Accessory / Separate Part Destination	For firmware version <= 2.4

Complementary

Net Weight	0.01 kg
------------	---------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	2.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	6 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	70
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	639 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration