



Discrete I/O module, Modicon TM3, 16 IO (8 digital inputs, 8 digital outputs, screw)

TM3RDM16R

EAN Code: 3606480696343



Main

Range Of Product	Modicon TM3
Product Or Component Type	Discrete I/O module
Range Compatibility	Modicon Easy M200
Discrete Input Number	8 for input conforming to IEC 61131-2 Type 1
Discrete Input Logic	Sink or source (positive/negative)
Discrete Input Voltage	24 V
Discrete Input Current	5 mA for input
Discrete Output Type	Relay normally open
Discrete Output Number	8
Discrete Output Logic	Positive or negative
Discrete Output Voltage	24 V DC for relay output 240 V AC for relay output
Discrete Output Current	2000 mA for relay output

Complementary

Discrete I/O Number	16
Current Consumption	70 mA at 5 V DC via bus connector (at state on) 40 mA at 24 V DC via bus connector (at state on)
Discrete Input Voltage Type	DC
Voltage State 1 Guaranteed	1528.8 V for input
Current State 1 Guaranteed	>= 2.5 mA (input)
Voltage State 0 Guaranteed	05 V for input
Current State 0 Guaranteed	<= 1 mA (input)
Input Impedance	4.7 kOhm
Response Time	4 ms (turn-on) 4 ms (turn-off)
Maximum Current Per Output Common	4 A
Mechanical Durability	20000000 cycles
Minimum Load	10 mA at 5 V DC for relay output
Local Signalling	1 LED per channel (green) for I/O state

11 x 1.5 mm² removable screw terminal block with pitch 3.81 mm adjustment for outputs
9 x 1.5 mm² removable screw terminal block with pitch 3.81 mm adjustment for inputs
Unshielded cable: <50 m for input
Unshielded cable: <150 m for output
Between input and internal logic at 500 V AC
Non-insulated between inputs
Between input groups and output groups at 1500 V AC
Between open contact at 750 V AC
Between output and internal logic at 500 V AC
Non-insulated between outputs
CE
Top hat type TH35-15 rail conforming to IEC 60715
Top hat type TH35-7.5 rail conforming to IEC 60715
plate or panel with fixing kit
90 mm
84.6 mm
27.4 mm
0.118 kg

Environment

Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 6 kV on contact conforming to IEC 61000-4-2
Resistance To Electromagnetic Fields	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8
Resistance To Fast Transients	2 kV for relay output conforming to IEC 61000-4-4 1 kV for input conforming to IEC 61000-4-4
Surge Withstand	2 kV output common mode conforming to IEC 61000-4-5 1 kV input common mode conforming to IEC 61000-4-5
Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6
Electromagnetic Emission	Radiated emissions - test level: 40 dBμV/m QP class A (10 m) at 30230 MHz conforming to IEC 55011 Radiated emissions - test level: 47 dBμV/m QP class A (10 m) at 2301000 MHz conforming to IEC 55011
Ambient Air Temperature For Operation	055 °C horizontal installation
Ambient Air Temperature For Storage	-2570 °C
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)
Ip Degree Of Protection	IP20 with protective cover in place
Pollution Degree	2
Operating Altitude	02000 m
Storage Altitude	03000 m
Vibration Resistance	3.5 mm at 58.4 Hz on DIN rail 1 gn at 8.4150 Hz on DIN rail 3.5 mm at 58.7 Hz on panel 2 gn at 8.7150 Hz on panel
Shock Resistance	15 gn for 11 ms

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	12.4 cm
Package 1 Width	7.2 cm
Package 1 Length	10.3 cm
Package 1 Weight	190 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	26
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5440 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	624
Package 3 Height	80 cm
Package 3 Width	120 cm
Package 3 Length	105 cm
Package 3 Weight	139560 g

Contractual warranty

Warranty 18 months

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

3 May 2024