Product datasheet

Specification





discrete I/O extension module - 10 I O - 12 V DC - for Zelio Logic

Local distributor code:

389838469 SR3XT101JD

EAN Code: 3389119203944

! To be discontinued

Main

Range Of Product	Zelio Logic
Product Or Component Type	Discrete I/O extension module

Complementary

Complementary	
Number Or Control Scheme Lines	120 with ladder programming
Cycle Time	690 ms
Backup Time	10 years at 25 °C
Clock Drift	12 min/year at 055 °C
Checks	Program memory on each power up
[Us] Rated Supply Voltage	12 V DC
Supply Voltage Limits	10.414.4 V
Reverse Polarity Protection	With
Discrete Input Number	6 conforming to IEC 61131-2 Type 1
Discrete Input Type	Resistive
Discrete Input Voltage	12 V DC
Discrete Input Current	4 mA
Counting Frequency	1 kHz for discrete input
Voltage State 1 Guaranteed	>= 7 V for IBIG used as discrete input circuit >= 5.6 V for I1IA and IHIR discrete input circuit
Voltage State 0 Guaranteed	<= 3 V for IBIG used as discrete input circuit <= 2.4 V for I1IA and IHIR discrete input circuit
Current State 1 Guaranteed	>= 2 mA (I1IA and IHIR discrete input circuit) >= 0.5 mA (IBIG used as discrete input circuit)
Current State 0 Guaranteed	<= 0.2 mA (IBIG used as discrete input circuit) <= 0.9 mA (I1IA and IHIR discrete input circuit)
Input Compatibility	3-wire proximity sensors PNP for discrete input
Input Impedance	14 kOhm for IBIG used as discrete input circuit 2.7 kOhm for I1IA and IHIR discrete input circuit
Number Of Outputs	4 relay
Output Voltage Limits	24250 V AC (relay output) 530 V DC (relay output)
Contacts Type And Composition	NO for relay output
Output Thermal Current	8 A for all 4 outputs for relay output

Pollution Degree Ambient Air Temperature For Operation	2 conforming to IEC 61131-2 -2040 °C in non-ventilated enclosure conforming to IEC 60068-2-1 and IEC 60068-2-2	
Pollution Degree	2 conforming to IEC 61131-2	
Pollution Degree	2 conforming to IEC 61121.2	
Disturbance Radiated/Conducted	Class B conforming to EN 55022-11 group 1	
	EMC directive conforming to IEC 61131-2 zone B Low voltage directive conforming to IEC 61131-2	
	EMC directive conforming to IEC 61000-6-4	
Environmental Characteristic	EMC directive conforming to IEC 61000-6-2 EMC directive conforming to IEC 61000-6-3	
	IP40 (front panel) conforming to IEC 60529	
Ip Degree Of Protection	IP20 (terminal block) conforming to IEC 60529	
	IEC 61000-4-6 level 3	
	IEC 60068-2-6 Fc IEC 61000-4-11	
	IEC 61000-4-3	
	IEC 61000-4-4 level 3 IEC 61000-4-2 level 3	
	IEC 61000-4-12 IEC 61000-4-4 level 3	
	IEC 61000-4-5	
Standards	IEC 60068-2-27 Ea	
	GOST	
	CSA C-Tick	
	UL 2014	
Product Certifications	GL	
Environment		
Net Weight	0.2 kg	
Overvoltage Category	III conforming to IEC 60664-1	
Tightening Torque	0.5 N.m	
	Screw terminals, 2 x 0.22 x 1.5 mm² (AWG 24AWG 16) solid	
	Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) solid	
	Screw terminals, 2 x 0.252 x 0.75 mm² (AWG 24AWG 18) flexible with cable end Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) semi-solid	
Connections - Terminals	Screw terminals, 1 x 0.251 x 2.5 mm² (AWG 24AWG 14) flexible with cable end	
	5 ms (from state 1 to state 0) for relay output	
Voltage Response Time	10 ms (from state 0 to state 1) for relay output	
[Uimp] Rated Impulse Withstand	4 kV conforming to EN/IEC 60947-1 and EN/IEC 60664-1	
Mechanical Durability	10000000 cycles for relay output	
Operating Rate In Hz	0.1 Hz (at le) for relay output 10 Hz (no load) for relay output	
	>= 10 mA at 12 V (relay output)	
	DC-13: 500000 cycles at 24 V, 0.6 A for relay output conforming to IEC 60947-5-1 DC-12: 500000 cycles at 24 V, 1.5 A for relay output conforming to IEC 60947-5-1	
Electrical Durability	AC-15: 500000 cycles at 230 V, 0.9 A for relay output conforming to IEC 60947-5-1 AC-12: 500000 cycles at 230 V, 1.5 A for relay output conforming to IEC 60947-5-1	

Number Of Units In Package 1

Package 1 Height	6.800 cm
Package 1 Width	9.000 cm
Package 1 Length	10.000 cm
Package 1 Weight	181.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.911 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	


Dimensions Drawings

I/O Extension Modules

Mounting on 35 mm/1.38 in. DIN Rail



Screw Fixing (Retractable Lugs)




SR3	a (mm/in.)	G (mm/in.)
XT61••	35 / 1.38	25 / 0.98
XT101••	72 / 2.83	60 / 2.36
XT141••	72 / 2.83	60 / 2.36

Connections and Schema

Connection of Smart Relays on DC Supply, with Discrete I/O Extension Modules

SR3B···JD + SR3XT···JD, SR3B···BD + SR3XT···BD



- (1) 1 A quick-blow fuse or circuit-breaker.
- (2) Ca: Analog sensor / Ta: Analog transmitter.
- (3) Recommended values: $2.2 \text{ k}\Omega / 0.5 \text{ W}$ (10 k Ω max.)
- (4) Screened cables, maximum length 10 m / 32.80 feet.


NOTE: QF and QG: 5 A for SR3XT141..

Performance Curves

Compact and Modular Smart Relays

Electrical Durability of Relay Outputs

(in millions of operating cycles, conforming to IEC/EN 60947-5-1) DC-12 (1)




X: Current (A)

Y: Millions of operating cycles

(1) DC-12: control of resistive loads and of solid state loads isolated by opto-coupler, L/R ≤ 1 ms.

DC-13 (1)



X: Current (A)

Y: Millions of operating cycles

(1) DC-13: switching electromagnets, $L/R \le 2 \times (Ue \times Ie)$ in ms, Ue: rated operational voltage, Ie: rated operational current (with a protection diode on the load, DC-12 curves must be used with a coefficient of 0.9 applied to the number in millions of operating cycles).