# **Product datasheet**

Specification





# digital input module - 12I - 24V DC sink - 1 wire

TM5SDI12D

EAN Code: 3595864074450

#### Main

Range Of Product	Modicon TM5
Product Or Component Type Discrete input module	
Discrete Input Number	12
Discrete Input Voltage	24 V

# Complementary

Range Compatibility	PacDrive LMC motion controller Modicon M258 Modicon LMC058		
Product Compatibility	Motion controller PacDrive LMC Pro PacDrive LMC Pro 2 Logic controller PacDrive LMC Eco		
Discrete Input Voltage Type	DC		
Input Voltage Limits	20.428.8 V		
Discrete Input Logic	Sink		
Discrete Input Current	3.75 mA		
Input Impedance	6.4 kOhm		
Colour	White		
Voltage State 0 Guaranteed	<= 5 V		
Voltage State 1 Guaranteed	>= 15 V		
Input Filtering	<= 25 ms configurable by software <= 100 ms hardware		
Isolation	500 Vrms AC insulation between channel and bus No insulation between channels		
Current Consumption	36 mA at 5 V DC bus 73 mA at 24 V DC all inputs On		
Maximum Power Dissipation In W	1.93 W		
Local Signalling	LED green for power supply     LED red for power supply     LEDs green for input status		
Electrical Connection	1 wire		
Marking	CE		
Net Weight	0.025 kg		

#### **Environment**



Standards	CSA C22.2 No 213 IEC 61131-2		
	UL 508		
	CSA C22.2 No 142		
Product Certifications	cULus		
	C-Tick		
	GOST-R		
	CSA		
Ambient Air Temperature For	-1055 °C without derating (horizontal installation)		
Operation	-1060 °C with derating factor (horizontal installation)		
	-1050 °C (vertical installation)		
Ambient Air Temperature For Storage	-4070 °C		
Relative Humidity	595 % without condensation		
Ip Degree Of Protection	IP20 conforming to IEC 61131-2		
Pollution Degree	2 conforming to IEC 60664		
Operating Altitude	02000 m		
Storage Altitude	03000 m		
Vibration Resistance	1 gn at 8.4150 Hz on DIN rail		
	3.5 mm at 58.4 Hz on DIN rail		
Shock Resistance	15 gn for 11 ms		
Electromagnetic Compatibility	Electrostatic discharge immunity test, 4 kV on contact conforming to IEC 61000-4-2 Electrostatic discharge immunity test, 8 kV in air conforming to IEC 61000-4-2 Susceptibility to electromagnetic fields, 1 V/m 22.7 GHz conforming to IEC 61000-4-3		
	Susceptibility to electromagnetic fields, 10 V/m 802000 MHz conforming to IEC 61000-4-3		
	Electrical fast transient/burst immunity test, 1 kV I/O conforming to IEC 61000-4-4		
	Electrical fast transient/burst immunity test, 1 kV shielded cable conforming to IEC 61000-4-4		
	Electrical fast transient/burst immunity test, 2 kV power lines conforming to IEC 61000-4-4		
	1.2/50 µs shock waves immunity test, 0.5 kV differential mode conforming to IEC 61000-4-5		
	1.2/50 µs shock waves immunity test, 1 kV common mode conforming to IEC 61000-4-5		
	Conducted RF disturbances conforming to IEC 61000-4-6		
	Conducted and radiated emissions conforming to CISPR 11		

# **Packing Units**

Unit Type Of Package 1 PCE  Number Of Units In Package 1 Package 1 Height 2.000 cm  Package 1 Width 6.000 cm  Package 1 Length 10.500 cm  Package 1 Weight 36.000 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 97  Package 2 Height 15.000 cm  Package 2 Width 30.000 cm  Package 2 Length 40.000 cm		
Package 1 Height 2.000 cm  Package 1 Width 6.000 cm  Package 1 Length 10.500 cm  Package 1 Weight 36.000 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 97  Package 2 Height 15.000 cm  Package 2 Width 30.000 cm  Package 2 Length 40.000 cm	Jnit Type Of Package 1	CE
Package 1 Width 6.000 cm  Package 1 Length 10.500 cm  Package 1 Weight 36.000 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 97  Package 2 Height 15.000 cm  Package 2 Width 30.000 cm  Package 2 Length 40.000 cm	Number Of Units In Package 1 1	
Package 1 Length 10.500 cm  Package 1 Weight 36.000 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 97  Package 2 Height 15.000 cm  Package 2 Width 30.000 cm  Package 2 Length 40.000 cm	Package 1 Height 2	.000 cm
Package 1 Weight 36.000 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 97  Package 2 Height 15.000 cm  Package 2 Width 30.000 cm  Package 2 Length 40.000 cm	Package 1 Width 6	.000 cm
Unit Type Of Package 2 S02  Number Of Units In Package 2 97  Package 2 Height 15.000 cm  Package 2 Width 30.000 cm  Package 2 Length 40.000 cm	Package 1 Length 1	0.500 cm
Number Of Units In Package 2 97  Package 2 Height 15.000 cm  Package 2 Width 30.000 cm  Package 2 Length 40.000 cm	Package 1 Weight 3	6.000 g
Package 2 Height         15.000 cm           Package 2 Width         30.000 cm           Package 2 Length         40.000 cm	Jnit Type Of Package 2	502
Package 2 Width         30.000 cm           Package 2 Length         40.000 cm	Number Of Units In Package 2 9	7
Package 2 Length 40.000 cm	Package 2 Height 1	5.000 cm
	Package 2 Width 3	0.000 cm
Daylore C. Weinkt	Package 2 Length 4	0.000 cm
Fackage 2 Weight 3.866 kg	Package 2 Weight 3	.866 kg

# **Contractual warranty**

Warranty

18 months

# Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
<b>Environmental Disclosure</b>	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

# TM5SDI12D

**Dimensions Drawings** 

## TM5 Slice


#### **Dimensions**




Mounting and Clearance


#### TM5 System


#### **Spacing Requirements**






#### Mounting on a DIN Rail







# **Product datasheet**

## TM5SDI12D

Connections and Schema


#### TM5 System Wiring Recommendations

#### Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in.	0.35		ß		
	mm²	0,082,5	0,252,5	0,251,5	2 x 0,252 x 0,75
	AWG	2814	2414	2416	2 x 242 x 18


#### Electronic Module 12DI 24 Vdc Sink 1 Wire

#### Wiring Diagrams



- (1) Internal electronics
- (2) 24 Vdc I/O power segment integrated into the bus bases
- (3) 2 wire-sensor
- (4) 24 Vdc I/O power segment by external connection

To connect 2-wire devices, you can add a TM5SPDD12F Common Distribution module:



(1) Internal electronics

# **Product datasheet**

## TM5SDI12D

- (2) 24 Vdc I/O power segment integrated into the bus bases (3) Integrated fuse type T slow-blow 6.3 A 250 V exchangeable
- (4) 2 wire-sensor