



# controller M241 24 IO relay Ethernet

TM241CE24R

EAN Code: 3606480648830

#### Main

Range Of Product	Modicon M241
Product Or Component Type	Logic controller
[Us] Rated Supply Voltage	100240 V AC
Discrete Input Number	14, discrete input 8 fast input conforming to IEC 61131-2 Type 1
Discrete Output Type	Relay Transistor
Discrete Output Number	6 relay 4 transistor 4 fast output
Discrete Output Voltage	5125 V DC for relay output 5250 V AC for relay output 24 V DC for transistor output
Discrete Output Current	2 A for relay output (Q4Q9) 0.1 A for fast output (PTO mode) (TR0TR3) 0.5 A for transistor output (TR0TR3)

# Complementary

Discrete I/O Number	24
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)
Supply Voltage Limits	85264 V
Network Frequency	50/60 Hz
Discrete Input Logic	Sink or source
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Voltage State 1 Guaranteed	>= 15 V for input
Voltage State 0 Guaranteed	<= 5 V for input
Discrete Input Current	5 mA for input
Input Impedance	4.7 kOhm for input
Response Time	50 μs turn-on, I0I13 terminal(s) for input
Configurable Filtering Time	1 μs for fast input
Discrete Output Logic	Positive logic (source)
Output Voltage Limits	125 V DC relay output 30 V DC transistor output 277 V AC relay output
Maximum Output Frequency	1 kHz for transistor output 20 kHz for fast output (PWM mode) 100 kHz for fast output (PLS mode)

Accuracy	+/- 0.1 % at 0.020.1 kHz for fast output +/- 1 % at 0.11 kHz for fast output
Protection Type	Short-circuit protection for transistor output Short-circuit and overload protection with automatic reset for transistor output Reverse polarity protection for transistor output Without protection for relay output
Reset Time	10 ms automatic reset output 12 s automatic reset fast output
Memory Capacity	64 MB for system memory RAM
Data Backed Up	128 MB built-in flash memory for backup of user programs
Data Storage Equipment	<= 16 GB SD card (optional)
Battery Type	BR2032 lithium non-rechargeable, battery life: 4 year(s)
Backup Time	2 years at 25 °C
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task 0.7 ms for other instruction
Application Structure	8 external event tasks 3 cyclic master tasks + 1 freewheeling task 8 event tasks 4 cyclic master tasks
Realtime Clock	With
Clock Drift	<= 60 s/month at 25 °C
Positioning Functions	PTO function 4 channel(s) (positioning frequency: 100 kHz)
Counting Input Number	4 fast input (HSC mode) at 200 kHz 14 standard input at 1 kHz
Control Signal Type	A/B at 100 kHz for fast input (HSC mode) Pulse/direction at 200 kHz for fast input (HSC mode) Single phase at 200 kHz for fast input (HSC mode)
Integrated Connection Type	Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface Non isolated serial link serial 2 with removable screw terminal block connector and RS485 interface USB port with mini B USB 2.0 connector Ethernet with RJ45 connector
Supply	(serial 1)serial link supply: 5 V, <200 mA
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for bus length of 3 m for USB 10/100 Mbit/s for Ethernet
Communication Port Protocol	Non isolated serial link: Modbus master/slave
Port Ethernet	10BASE-T/100BASE-TX - 1 port(s) copper cable
Ethernet Services	FDR DHCP server via TM4 Ethernet switch network module DHCP client embedded Ethernet port SMS notifications Updating firmware SNMP client/server Programming NGVL Monitoring IEC VAR ACCESS FTP client/server Downloading SQL client Modbus TCP client I/O scanner Ethernet/IP originator I/O scanner embedded Ethernet port Ethernet/IP target, Modbus TCP server and Modbus TCP slave Send and receive email from the controller based on TCP/UDP library Web server (WebVisu & XWeb system) OPC UA server DNS client

Local Signalling	1 LED (green) for PWR
	1 LED (green) for RUN
	1 LED (red) for module error (ERR)
	1 LED (red) for I/O error (I/O)
	1 LED (green) for SD card access (SD)
	1 LED (red) for BAT
	1 LED (green) for SL1
	1 LED (green) for SL2
	1 LED (red) for bus fault on TM4 (TM4)
	1 LED per channel (green) for I/O state
	1 LED (green) for Ethernet port activity
Electrical Connection	removable screw terminal blockfor inputs and outputs (pitch 5.08 mm)
	removable screw terminal blockfor connecting the 24 V DC power supply (pitch 5.08
	mm)
Maximum Cable Distance	Unshielded cable: <50 m for input
Between Devices	Shielded cable: <10 m for fast input
	Unshielded cable: <50 m for output
	Shielded cable: <3 m for fast output
	Officiaca cable. 40 fff for last output
Insulation	Between supply and internal logic at 500 V AC
	Non-insulated between supply and ground
Marking	CE
Sensor Power Supply	24 V DC at 400 mA supplied by the controller
Surge Withstand	2 kV power lines (AC) common mode conforming to IEC 61000-4-5
	2 kV relay output common mode conforming to IEC 61000-4-5
	1 kV shielded cable common mode conforming to IEC 61000-4-5
	1 kV power lines (AC) differential mode conforming to IEC 61000-4-5
	1 kV relay output differential mode conforming to IEC 61000-4-5
	1 kV input common mode conforming to IEC 61000-4-5
	1 kV transistor output common mode conforming to IEC 61000-4-5
Web Services	Web server
Maximum Number Of	8 Modbus server
Connections	8 SoMachine protocol
	10 web server
	4 FTP server
	16 Ethernet/IP target
	8 Modbus client
Number Of Server Device(S)	64 Modbus TCP:
	16 EtherNet/IP:
Cycle Time	10 ms 16 EtherNet/IP
•	64 ms 64 Modbus TCP
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715
	Top hat type TH35-13 rail conforming to IEC 60715
	plate or panel with fixing kit
Height	90 mm
Depth	95 mm
Width	150 mm
Net Weight	0.53 kg
TTOE TTOISITE	0.53 kg

# **Environment**

Standards ANSI/ISA 12-12-01

CSA C22.2 No 142 CSA C22.2 No 213

IEC 61131-2:2007 Marine specification (LR, ABS, DNV, GL) UL 508

Product Certifications	DCM	
Froduct Certifications	RCM cULus	
	CE	
	UKCA	
	DNV-GL ABS	
	LR	
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2	
Resistance To Electromagnetic	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3	
Fields	3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3	
	1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3	
Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4	
	2 kV (relay output) conforming to IEC 61000-4-4	
	1 kV (Ethernet line) conforming to IEC 61000-4-4	
	1 kV (serial link) conforming to IEC 61000-4-4 1 kV (input) conforming to IEC 61000-4-4	
	1 kV (transistor output) conforming to IEC 61000-4-4	
Resistance To Conducted	10 V 0.1580 MHz conforming to IEC 61000-4-6	
Disturbances	3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL)	
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to	
	Marine specification (LR, ABS, DNV, GL)	
Electromagnetic Emission	Conducted emissions - test level: 12069 dBµV/m QP ( power lines) at 10150 kHz	
	conforming to IEC 55011	
	Conducted emissions - test level: 63 dBµV/m QP ( power lines) at 1.530 MHz conforming to IEC 55011	
	Conducted emissions - test level: 79 dBµV/m QP/66 dBµV/m AV ( power lines) at	
	0.150.5 MHz conforming to IEC 55011	
	Conducted emissions - test level: 73 dB $\mu$ V/m QP/60 dB $\mu$ V/m AV ( power lines) at	
	0.5300 MHz conforming to IEC 55011	
	Radiated emissions - test level: 40 dBμV/m QP class A ( 10 m) at 30230 MHz conforming to IEC 55011	
	Conducted emissions - test level: 7963 dBµV/m QP ( power lines) at 1501500	
	kHz conforming to IEC 55011	
	Radiated emissions - test level: 47 dBμV/m QP class A ( 10 m) at 2301000 MHz	
	conforming to IEC 55011	
Immunity To Microbreaks	10 ms	
Ambient Air Temperature For Operation	-1050 °C (vertical installation) -1055 °C (horizontal installation)	
Ambient Air Temperature For Storage	-2570 °C	
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)	
Ip Degree Of Protection	IP20 with protective cover in place	
Pollution Degree	2	
Operating Altitude	02000 m	
Storage Altitude	03000 m	
Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail	
	3 gn at 8.4150 Hz on symmetrical rail	
	3.5 mm at 58.4 Hz on panel mounting 3 gn at 8.4150 Hz on panel mounting	
Shock Resistance		
550n Nooistanio	15 gn for 11 ms	
Packing Units		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	11.208 cm	
Package 1 Width	13.04 cm	
	13.04 CIII	

Package 1 Weight	760.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.97 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	64
Package 3 Height	75.0 cm
Package 3 Width	40.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	66 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	

#### **Certifications & Standards**


Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Environmental Disclosure</b>	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration


# **Product datasheet**

## **TM241CE24R**

## **Dimensions Drawings**

#### **Dimensions**







## **TM241CE24R**


Mounting and Clearance

#### Clearance






#### **Mounting Position**




#### **Acceptable Mounting**




**NOTE:** Expansion modules must be mounted above the logic controller.

#### **Incorrect Mounting**



#### **Direct Mounting On a Panel Surface**


#### **Mounting Hole Layout**



#### Connections and Schema

#### **Digital Inputs**


#### Wiring Diagram (Positive Logic)



(\*): Type T fuse

(1): The COM0, COM1 and COM2 terminals are not connected internally.

#### Wiring Diagram (Negative Logic)




(\*): Type T fuse

(1): The COM0, COM1 and COM2 terminals are not connected internally.

#### **Fast Transistor Outputs**


#### Wiring Diagram



(\*): 2 A fast-blow fuse


#### **Relay Outputs**

#### Wiring Diagram



- (\*): Type T fuse
- (1): The terminals COM1 to COM4 are not connected internally.
- (2): To improve the life time of the contacts, and to protect from potential inductive load damage, you must connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load

#### **USB Mini-B Connection**



#### **Ethernet Connection to a PC**

