Specifications





# controller M251 Ethernet CAN

TM251MESC

EAN Code: 3606480648861

### Main

Range Of Product	Modicon M251
Product Or Component Type	Logic controller
[Us] Rated Supply Voltage	24 V DC

## Complementary

oompiementai y	
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)
Supply Voltage Limits	20.428.8 V
Inrush Current	50 A
Power Consumption In W	32.640.4 W (with max number of I/O expansion module)
Memory Capacity	64 MB for system memory RAM
Data Backed Up	128 MB built-in flash memory for backup of user programs
Data Storage Equipment	<= 16 GB SD card (optional)
Battery Type	BR2032 lithium non-rechargeable, battery life: 4 year(s)
Backup Time	2 years at 25 °C
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task 0.7 ms for other instruction
Application Structure	3 cyclic master tasks + 1 freewheeling task 8 event tasks 4 cyclic master tasks 8 external event tasks
Realtime Clock	With
Clock Drift	<= 60 s/month at 25 °C
Integrated Connection Type	USB port with mini B USB 2.0 connector Non isolated serial link serial with RJ45 connector and RS232/RS485 interface Dual-port Ethernet with RJ45 connector CANopen J1939 with SUB-D 9 connector
Supply	(serial)serial link supply: 5 V, <200 mA
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for bus length of 3 m for USB
Communication Port Protocol	USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network
Port Ethernet	Ethernet marking 10BASE-T/100BASE-TX - 2 copper cable
Web Services	Web server

Communication Service	DHCP client
	Downloading
	Ethernet/IP slave device
	IEC VAR ACCESS
	Modbus TCP client
	Modbus TCP server
	Modbus TCP slave device
	Monitoring
	NGVL
	Programming
	Updating firmware
	SMS notifications
	FTP client/server
	SNMP client/server
	SQL client
	Send and receive email from the controller based on TCP/UDP library
	Web server (WebVisu & XWeb system)
	OPC UA server
	DNS client
Maximum Number Of	8 Modbus server
Connections	8 Modbus client
	16 Ethernet/IP target
	4 FTP server
	10 web server
	8 SoMachine protocol
Canopen Feature Profile	DR 303-1
	DS 301 V4.02
Number Of Server Device(S)	63 CANopen:
Local Signalling	1 LED (green) for PWR
	1 LED (green) for RUN
	1 LED (red) for module error (ERR)
	1 LED (red) for I/O error (I/O)
	1 LED (green) for SD card access (SD)
	1 LED (red) for BAT
	1 LED (green) for Ethernet port activity
	1 LED (green) for SL
	1 LED (red) for bus fault on TM4 (TM4)
	1 LED (green) for CANopen run
	1 LED (green) for CANopen error
Electrical Connection	removable screw terminal blockpower supply (pitch 5.08 mm)
Insulation	Non-insulated between supply and internal logic
	Between supply and ground at 500 V AC
Marking	CE
Surge Withstand	1 kV shielded cable common mode conforming to IEC 61000-4-5
-	1 kV power lines common mode conforming to IEC 61000-4-5
	0.5 kV power lines differential mode conforming to IEC 61000-4-5
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715
	Top hat type TH35-7.5 rail conforming to IEC 60715
	plate or panel with fixing kit
Height	90 mm
Depth	95 mm
Width	54 mm
Net Weight	0.22 kg

# Environment

Standards

ANSI/ISA 12-12-01 CSA C22.2 No 142 CSA C22.2 No 213 IEC 61131-2:2007 Marine specification (LR, ABS, DNV, GL) UL 508

Product Certifications	CULus CE
	UKCA
	DNV-GL
	ABS LR
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2
Resistance To Electromagnetic	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3
Fields	3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3
	1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3
Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4
	1 kV (Ethernet line) conforming to IEC 61000-4-4
	1 kV (serial link) conforming to IEC 61000-4-4
Resistance To Conducted	10 V 0.1580 MHz conforming to IEC 61000-4-6
Disturbances	3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL)
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to
	Marine specification (LR, ABS, DNV, GL)
Electromagnetic Emission	Conducted emissions - test level: 12069 dBµV/m QP ( power lines) at 10150 kHz
	conforming to IEC 55011
	Conducted emissions - test level: 63 dBµV/m QP ( power lines) at 1.530 MHz
	conforming to IEC 55011
	Radiated emissions - test level: 40 dBµV/m QP class A ( 10 m) at 30…230 MHz
	conforming to IEC 55011
	Conducted emissions - test level: 7963 dBµV/m QP ( power lines) at 1501500 kHz conforming to IEC 55011
	Radiated emissions - test level: 47 dBµV/m QP class A ( 10 m) at 2301000 MHz
	conforming to IEC 55011
Immunity To Microbreaks	10 ms
Ambient Air Temperature For	-1035 °C (vertical installation)
Operation	-1055 °C (horizontal installation)
Ambient Air Temperature For Storage	-2570 °C
Relative Humidity	1095 %, without condensation (in operation)
	1095 %, without condensation (in storage)
Ip Degree Of Protection	IP20 with protective cover in place
Pollution Degree	2
Operating Altitude	02000 m
Storage Altitude	03000 m
Vibration Resistance	3.5 mm at 5…8.4 Hz on symmetrical rail
	3 gn at 8.4150 Hz on symmetrical rail
	3.5 mm at 58.4 Hz on panel mounting
	3 gn at 8.4150 Hz on panel mounting
Shock Resistance	15 gn for 11 ms
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
	-

51 0	
Number Of Units In Package 1	1
Package 1 Height	10.632 cm
Package 1 Width	11.868 cm
Package 1 Length	16.721 cm
Package 1 Weight	380.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30 cm

Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.461 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	80
Package 3 Height	75.0 cm
Package 3 Width	40.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	43 kg

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance


Mercury Free
Rohs Exemption Information Yes
Pvc Free


### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

### **Dimensions Drawings**


#### Dimensions






### Mounting and Clearance

#### Clearance




**Mounting Position** 




NOTE: Keep adequate spacing for proper ventilation and to maintain an ambient temperature between -10°C (14°F) and 55°C (131°F).

#### Acceptable Mounting




NOTE: Expansion modules must be mounted above the controller.

#### **Incorrect Mounting**



#### **Direct Mounting on a Panel Surface**



Connections and Schema

#### USB Connection to a PC




#### Ethernet Connection to a PC



### CANopen

#### Wiring



Pin	Signal	Description
1	-	Reserved
2	CAN_L	CAN_L bus line
3	CAN_GND	CAN ground
4	-	Reserved
5	(CAN_SHLD)	Optional CAN shield
6	GND	Ground
7	CAN_H	CAN_H bus line
8	-	Reserved
9	(CAN_V+)	Optional CAN external positive supply