## **Product datasheet**

Specifications





# Modicon TM3 - 4 analog inputs, 2 analog output (spring) 24Vdc

TM3AM6G

EAN Code: 3606480648953

## Main

| Range Of Product          | Modicon TM3                |
|---------------------------|----------------------------|
| Product Or Component Type | Input/output analog module |
| Range Compatibility       | Modicon M221               |
|                           | Modicon M241               |
|                           | Modicon M251               |
|                           | Modicon M262               |
| Analogue Input Number     | 4                          |
| Analogue Input Type       | current 420 mA             |
|                           | current 020 mA             |
|                           | voltage 010 V              |
|                           | voltage - 1010 V           |
| Analogue Output Number    | 2                          |
| Analogue Output Type      | Current: 420 mA            |
|                           | Current: 020 mA            |
|                           | Voltage: 010 V             |
|                           | Voltage: - 1010 V          |
|                           |                            |

## Complementary

| -                               |   |
|---------------------------------|---|
| Analogue Input Resolution       | 12 bits   |
|                                 | 11 bits + sign                                    |
| Permissible Continuous Overload | 13 V, analogue input type: voltage                |
|                                 | 40 mA, analogue input type: current               |
| Input Impedance                 | <= 50 Ohm current                                 |
|                                 | >= 1 MOhm voltage                                 |
| Analogue Output Resolution      | 12 bits   |
|                                 | 11 bits + sign                                    |
| Lsb Value                       | 2.44 mV 010 Vvoltage                              |
|                                 | 4.88 mV - 1010 Vvoltage                           |
|                                 | 4.88 μA 020 mAcurrent                             |
|                                 | 3.91 µA 420 mAcurrent                             |
| Load Type                       | Resistive   |
| Load Impedance Ohmic            | 1 kOhm voltage                                    |
|                                 | 300 Ohm current                                   |
| Stabilisation Time              | 1 ms  |
| Conversion Time                 | 1 ms + 1 ms per channel + 1 controller cycle time |
| Sampling Duration               | 1 ms  |
|                                 | 10 ms   |
| Absolute Accuracy Error         | +/- 1 % of full scale                             |
|                                 | +/- 0.2 % of full scale at 25 °C                  |
| Temperature Drift               | +/- 0.01 %FS/°C                                   |

| +/-0.5 %FS for input<br>+/-0.5 %FS for output  |
|--|
| +/- 0.2 %FS  |
| 20 mV  |
| <= 1 LSB   |
| 24 V DC  |
| 20.428.8 V   |
| Twisted shielded pairs cable <30 m for input/output circuit  |
| 45 mA at 5 V DC via bus connector no load<br>55 mA at 5 V DC via bus connector full load<br>55 mA at 24 V DC via external supply no load<br>100 mA at 24 V DC via external supply full load  |
| 1 LED (green) for PWR  |
| 10 x 1.5 mm <sup>2</sup> removable spring terminal block with pitch 3.81 mm adjustment for inputs<br>10 x 1.5 mm <sup>2</sup> removable spring terminal block with pitch 3.81 mm adjustment for inputs, outputs and supply                     |
| Between input and supply at 1500 V AC<br>Between input and internal logic at 500 V AC<br>Between output and supply at 1500 V AC<br>Between output and internal logic at 500 V AC   |
| CE   |
| 1 kV power supply common mode conforming to IEC 61000-4-5<br>0.5 kV power supply differential mode conforming to IEC 61000-4-5<br>1 kV I/O common mode conforming to IEC 61000-4-5<br>0.5 kV I/O differential mode conforming to IEC 61000-4-5 |
| Top hat type TH35-15 rail conforming to IEC 60715<br>Top hat type TH35-7.5 rail conforming to IEC 60715<br>plate or panel with fixing kit  |
| 90 mm  |
| 70 mm  |
| 23.6 mm  |
| 0.1 kg   |
|  |

## Environment

| Standards                                | IEC 61131-2  |
|--|--|
| Product Certifications                   | CE<br>UKCA<br>RCM<br>EAC<br>cULus<br>cULus HazLoc  |
| Resistance To Electrostatic<br>Discharge | 8 kV in air conforming to IEC 61000-4-2<br>4 kV on contact conforming to IEC 61000-4-2   |
| Resistance To Electromagnetic<br>Fields  | 10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3<br>3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3<br>1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3                             |
| Resistance To Magnetic Fields            | 30 A/m conforming to IEC 61000-4-8   |
| Resistance To Fast Transients            | 1 kV (I/O) conforming to IEC 61000-4-4   |
| Resistance To Conducted<br>Disturbances  | 10 V 0.1580 MHz conforming to IEC 61000-4-6<br>3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to<br>Marine specification (LR, ABS, DNV, GL) |

| Electromagnetic Emission                 | Radiated emissions - test level: 40 dB $\mu$ V/m QP class A (10 m) at 30230 MHz conforming to IEC 55011<br>Radiated emissions - test level: 47 dB $\mu$ V/m QP class A (10 m) at 2301000 MHz conforming to IEC 55011 |
|--|--|
| Immunity To Microbreaks                  | 10 ms  |
| Ambient Air Temperature For<br>Operation | -1055 °C horizontal installation<br>-1035 °C vertical installation   |
| Ambient Air Temperature For<br>Storage   | -2570 °C   |
| Relative Humidity                        | 1095 %, without condensation (in operation)<br>1095 %, without condensation (in storage)   |
| Ip Degree Of Protection                  | IP20   |
| Pollution Degree                         | 2  |
| Operating Altitude                       | 02000 m  |
| Storage Altitude                         | 03000 m  |
| Vibration Resistance                     | 3.5 mm at 5…8.4 Hz on DIN rail<br>3 gn at 8.4…150 Hz on DIN rail   |
| Shock Resistance                         | 15 gn for 11 ms  |

## **Packing Units**

| PCE      |
|----------|
| 1        |
| 7.5 cm   |
| 12.5 cm  |
| 10.5 cm  |
| 195.0 g  |
| \$02     |
| 9        |
| 15 cm    |
| 30 cm    |
| 40 cm    |
| 2.294 kg |
| P12      |
| 144      |
| 75 cm    |
| 120 cm   |
| 80 cm    |
| 46 kg    |
|          |

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free


## **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration   |
| China Rohs Regulation    | China RoHS declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | End of Life Information   |

## **Product datasheet**

### **Dimensions Drawings**


#### Dimensions




(\*) 8.5 mm/0.33 in when the clamp is pulled out.

Mounting and Clearance

### Spacing Requirements




#### Mounting on a Rail




#### **Incorrect Mounting**





(1) Install a mounting strip

#### Mounting Hole Layout




## **Product datasheet**

Connections and Schema

#### Analogue Mixed I/O Module

#### Wiring Diagram (Current / Voltage)



- (\*) Type T fuse
- (1) Current/Voltage analog output device
- (2) Current/Voltage analog input device