# **Product datasheet**

Specification





# compact I/O expansion block TM5 - 20 I/O - 12 DI - 8 DO transistor

TM5C12D8T

EAN Code: 3595864074368

## Main

Range Of Product	Modicon TM5	
Product Or Component Type	Compact I/O expansion block	

# Complementary

· · · · · · · · · · · · · · · · · ·				
Enclosure Material	Plastic			
Colour	White			
Input/Output Number	20			
For Enclosure Nominal Dimensions	ominal 12 I + 8 O			
Number Of Modules	Digital input: 3 module(s) x 4 Digital output: 2 module(s) x 4			
Discrete Input Number	12			
Discrete Input Voltage	24 V			
Discrete Input Voltage Type	DC			
Input Voltage Limits	20.428.8 V			
Discrete Input Logic	Sink			
Discrete Input Current	3.75 mA			
Input Impedance	6.4 kOhm			
Analogue Input Number	Input Number 0			
Discrete Output Number	8			
Discrete Output Type	Transistor			
Wiring Mode	3-wire for discrete input 3-wire for discrete output			
Output Voltage	24 V DC			
Output Voltage Limits	20.428.8 V DC			
Discrete Output Logic	Source			
Discrete Output Current	rrent 0.5 A per output			
Peak Output Current	4 A			
Voltage State 0 Guaranteed	<= 5 V			
Voltage State 1 Guaranteed	e 1 Guaranteed >= 15 V			
Input Filtering	<= 100 ms hardware <= 25 ms configurable by software			
Response Time	<= 300 μs from state 0 to state 1 for output <= 300 μs from state 1 to state 0 for output			

Maximum Leakage Current	5 μA (when switched off) for output			
Isolation	500 Vrms AC insulation between channel and bus No insulation between channels			
Maximum Voltage Drop	<0.3 V at 500 mA for output			
Current Consumption	68 mA at 5 V DC bus 80 mA at 24 V DC input/output			
Max Current	1000 mA sensor supply 1500 mA actuator supply 4000 mA loads on I/O power segment			
Maximum Power Dissipation In W 2.36 W				
Local Signalling	5 LEDs (green) for power supply 5 LEDs (red) for power supply 12 LEDs (green) for input status 8 LEDs (yellow) for output status			
Sensor Power Supply	24 V, 500 mA for all channels with overload, short-circuit and reverse polarity protection			
Electrical Connection	Removable spring terminal block			
Marking	CE			
Surge Withstand	0.5 kV differential mode 24 V DC conforming to IEC 61000-4-5 1 kV common mode 24 V DC conforming to IEC 61000-4-5			
Electromagnetic Compatibility	EN/IEC 61000-4-6			
Disturbance Radiated/Conducted	CISPR 11			

# **Environment**

IEC 61131-2 UL 508 CSA C22.2 No 213 CSA C22.2 No 142			
C-Tick GOST-R CSA cULus			
-1050 °C (vertical installation) -1060 °C (horizontal installation)			
-4070 °C			
595 % without condensation			
IP20 conforming to IEC 61131-2			
2 conforming to IEC 60664			
titude 02000 m			
03000 m			
1 gn at 8.4150 Hz on DIN rail 3.5 mm at 58.4 Hz on DIN rail			
15 gn for 11 ms			
4 kV on contact conforming to IEC 61000-4-2 8 kV in air conforming to IEC 61000-4-2			
1 V/m 22.7 GHz conforming to IEC 61000-4-3 10 V/m 802000 MHz conforming to IEC 61000-4-3			
1 kV (I/O) conforming to IEC 61000-4-4 1 kV (shielded cable) conforming to IEC 61000-4-4 2 kV (power lines) conforming to IEC 61000-4-4			
nting Support DIN rail			

Net Weight 0.24 kg

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	9.100 cm
Package 1 Length	11.000 cm
Package 1 Weight	273.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	36
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.171 kg

# **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium\*

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
<b>Environmental Disclosure</b>	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

Presentation

## TM5 Compact I/O Module





N°	Designation
1	Input electronic module / 4 digital inputs
2	Output electronic module / 4 digital outputs

# **Dimensions Drawings**

# Compact I/O Module

#### **Dimensions**







Mounting and Clearance


## TM5 System


#### **Spacing Requirements**






#### Mounting on a DIN Rail







# **Product datasheet**

## **TM5C12D8T**

Connections and Schema

## TM5 System Wiring Recommendations


#### Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in.	0.35		Ω		
	mm²	0,082,5	0,252,5	0,251,5	2 x 0,252 x 0,75
	AWG	2814	2414	2416	2 x 242 x 18

19 May 2024

#### Digital Input 4In


#### Wiring Diagram



- 1 Internal electronics
- 2 24 Vdc I/O power segment integrated into the bus bases
- 3 3-wire sensor
- 4 2-wire sensor

#### **Digital Output 4Out**


#### Wiring Diagram



- 1 Internal electronics
- 2 24 Vdc I/O power segment integrated into the bus bases
- 3 Inductive load protection
- 4 2-wire load
- 5 3-wire load

#### Performance Curves

## **Switching Inductive Load Characteristics**



- (1) Load resistance in  $\Omega$
- (2) Load inductance in H
- (3) Max. operating cycles / second