Specifications





## analog input module - 4I temperature probe PT100/PT1000 - 16 bits

TM5SAI4PH

EAN Code: 3595864074771

### Main

Range Of Product	Modicon TM5			
Product Or Component Type	Analog input module			
Analogue Input Number	4			
Analogue Input Type	Pt 100/Pt 1000 temperature probe - 200850 °C			
Analogue Input Resolution	16 bits			

## Complementary

Complementary					
Range Compatibility	Modicon LMC058 Modicon M258				
Product Compatibility	Logic controller Motion controller				
Measurement Resolution	0.1 °C				
Colour	White				
Measurement Error	< 0.037 % of full scale - 200850 °C Pt 100/Pt 1000 at 25 °C				
Temperature Coefficient	0.004 %FS/°C, analogue input type: temperature probe				
Non-Linearity	0.001 %FS, analogue input type: temperature probe				
Type Of Cable	Shielded cable				
Isolation	No insulation between channels 500 Vrms AC insulation between channel and bus				
Supply	Internal				
[Us] Rated Supply Voltage	24 V DC -1520 %				
Common Mode Rejection	> 95 dB				
Local Signalling	1 LED green for power supply 1 LED red for power supply 4 LEDs green for input status				
Current Consumption	2 mA at 5 V DC bus 46 mA at 24 V DC input/output				
Maximum Power Dissipation In W	1.11 W				
Marking	CE				
Net Weight	0.025 kg				

### Environment

Standards

UL 508 CSA C22.2 No 213 IEC 61131-2 CSA C22.2 No 142

Product Certifications	GOST-R				
	CSA				
	C-Tick				
	cULus				
	culus				
Ambient Air Temperature For	055 °C without derating (horizontal installation)				
Operation	060 °C with derating factor (horizontal installation)				
	050 °C (vertical installation)				
Ambient Air Temperature For	-2570 °C				
Storage					
Relative Humidity	595 % without condensation				
Ip Degree Of Protection	IP20 conforming to IEC 61131-2				
Pollution Degree	2 conforming to IEC 60664				
On a making a Alkikuda	0				
Operating Altitude	02000 m				
Storage Altitude	03000 m				
	0				
Vibration Resistance	1 gn at 8.4…150 Hz on DIN rail				
	3.5 mm at 58.4 Hz on DIN rail				
Shock Resistance	15 gn for 11 ms				
	•				
Resistance To Electrostatic	4 kV on contact conforming to IEC 61000-4-2				
Discharge	8 kV in air conforming to IEC 61000-4-2				
Resistance To Electromagnetic	1 V/m 22.7 GHz conforming to IEC 61000-4-3				
Fields	10 V/m 802000 MHz conforming to IEC 61000-4-3				
<b>Resistance To Fast Transients</b>	1 kV (I/O) conforming to IEC 61000-4-4				
	1 kV (shielded cable) conforming to IEC 61000-4-4				
	2 kV (power lines) conforming to IEC 61000-4-4				
Surge Withstand	0.5 kV differential mode conforming to IEC 61000-4-5				
	1 kV common mode conforming to IEC 61000-4-5				
	· · · · · · · · · · ·				
Electromagnetic Compatibility	I/IEC 61000-4-6				
Disturbance Radiated/Conducted	CISPR 11				

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	6.0 cm
Package 1 Length	10.5 cm
Package 1 Weight	41.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	97
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.977 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

### **Certifications & Standards**

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

**Dimensions Drawings** 

#### TM5 Slice


#### Dimensions

mm in. 75 2.95 0.49 0.49 0.66 67 67


Mounting and Clearance

#### TM5 System

#### **Spacing Requirements**



#### Mounting on a DIN Rail



Connections and Schema

#### TM5 System Wiring Recommendations


#### Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in.	9 0.35		å		æ
	mm <sup>2</sup>	0,082,5	0,252,5	0,251,5	2 x 0,252 x 0,75
	AWG	2814	2414	2416	2 x 242 x 18

#### Electronic Module 4AI PT100/PT1000 16 Bits

#### Wiring Diagrams

The following figure shows the 2-wire wiring diagram:




(1) Internal electronics

(2) 24 Vdc I/O power segment integrated into the bus bases

(3) 2-wire sensor

(S) Sensor

The following figure shows the 3-wire and 4-wire wiring diagram:



(1) Internal electronics

- (2) 24 Vdc I/O power segment integrated into the bus bases
- (3) 3-wire sensor
- (4) 4-wire sensor

(S) Sensor