

Product datasheet

Specifications



empty pendant control station XAC-A - 3 vertical openings

Local distributor code:
398218287 XACA03H7

EAN Code: 3389118117686

Main

| | |
|---------------------------|-------------------------|
| Range Of Product | Harmony XAC |
| Product Or Component Type | Pendant control station |
| Device Short Name | XACA |

Complementary

| | |
|---------------------------------------|--|
| Control Station Type | Double insulated |
| Enclosure Material | Polypropylene |
| Electrical Circuit Type | Control circuit |
| Enclosure Type | Empty enclosure |
| Number Of Cut-Out | 3 cut-outs |
| Control Station Colour | Yellow |
| Cable Entry | Rubber sleeve with stepped entry 8...26 mm |
| Guard Rail | Without |
| Vertical Operator Cut-Out Centre | 30 mm |
| Standards | UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 |
| Product Certifications | CSA GOST UL CCC |
| Protective Treatment | TH |
| Ambient Air Temperature For Operation | -25...70 °C |
| Ambient Air Temperature For Storage | -40...70 °C |
| Vibration Resistance | 15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6 |
| Shock Resistance | 100 gn conforming to IEC 60068-2-27 |
| Overvoltage Category | Class II conforming to IEC 61140 |
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |
| Ik Degree Of Protection | IK08 conforming to EN 50102 |
| Mechanical Durability | 1000000 cycles |
| Net Weight | 0.44 kg |

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.5 cm |
| Package 1 Width | 9.0 cm |
| Package 1 Length | 44.5 cm |
| Package 1 Weight | 500.0 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |


Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Dimensions Drawings

Dimensions

Below drawing shows a product with 6 cut-outs. Select the number of cut-outs according to the product characteristics in order to get b, b1 and c dimensions.



- (1) For 2 and 3-way XAC A stations.
(2) For 4 to 8-way XAC A stations.
(3) With trigger action Emergency stop head operator
(4) Internal ø

Dimensions in mm

| Number of cut-outs | 2 | 3 | 4 | 5 | 6 | 8 | 12 |
|--------------------|-----|-----|-----|-----|-----|-----|-----|
| b | 314 | 314 | 440 | 440 | 500 | 560 | 680 |
| b1 | 190 | 190 | 250 | 250 | 310 | 370 | 490 |
| c | 80 | 80 | 80 | 80 | 80 | 80 | 92 |

Dimensions in in.

| Number of cut-outs | 2 | 3 | 4 | 5 | 6 | 8 | 12 |
|--------------------|-------|-------|-------|-------|-------|-------|-------|
| b | 12.36 | 12.36 | 17.32 | 17.32 | 19.68 | 22.05 | 26.77 |
| b1 | 7.48 | 7.48 | 9.84 | 9.84 | 12.20 | 14.57 | 19.29 |

| Number of cut-outs | 2 | 3 | 4 | 5 | 6 | 8 | 12 |
|--------------------|------|------|------|------|------|------|------|
| c | 3.15 | 3.15 | 3.15 | 3.15 | 3.15 | 3.15 | 3.62 |