# **Product datasheet**

Specifications





# empty pendant control station XAC-A - 6 vertical openings

Local distributor code: 2220176

XACA06

EAN Code: 3389110645064

#### Main

| Range Of Product          | Harmony XAC             |  |  |
|---------------------------|-------------------------|--|--|
| Product Or Component Type | Pendant control station |  |  |
| Device Short Name         | XACA                    |  |  |

#### Complementary

| complementary                            |  |  |  |  |  |  |  |
|--|--|--|--|--|--|--|--|
| Control Station Type                     | Double insulated   |  |  |  |  |  |  |
| Enclosure Material                       | Polypropylene  |  |  |  |  |  |  |
| Electrical Circuit Type                  | Control circuit  |  |  |  |  |  |  |
| Enclosure Type                           | mpty enclosure   |  |  |  |  |  |  |
| Number Of Cut-Out                        | δ cut-outs   |  |  |  |  |  |  |
| Control Station Colour                   | Yellow   |  |  |  |  |  |  |
| Cable Entry                              | Rubber sleeve with stepped entry 826 mm                    |  |  |  |  |  |  |
| Guard Rail                               | Without  |  |  |  |  |  |  |
| Vertical Operator Cut-Out Centre         | 30 mm  |  |  |  |  |  |  |
| Standards                                | IEC 60204-32<br>UL 508<br>CSA C22.2 No 14<br>IEC 60947-5-1 |  |  |  |  |  |  |
| Product Certifications                   | GOST<br>CCC  |  |  |  |  |  |  |
| Protective Treatment                     | тн   |  |  |  |  |  |  |
| Ambient Air Temperature For<br>Operation | -2570 °C   |  |  |  |  |  |  |
| Ambient Air Temperature For<br>Storage   | -4070 °C   |  |  |  |  |  |  |
| Vibration Resistance                     | 15 gn (f= 10500 Hz) conforming to IEC 60068-2-6            |  |  |  |  |  |  |
| Shock Resistance                         | 100 gn conforming to IEC 60068-2-27                        |  |  |  |  |  |  |
| Overvoltage Category                     | Class II conforming to IEC 61140                           |  |  |  |  |  |  |
| Ip Degree Of Protection                  | IP65 conforming to IEC 60529                               |  |  |  |  |  |  |
| Ik Degree Of Protection                  | IK08 conforming to IEC 62262                               |  |  |  |  |  |  |
| Mechanical Durability                    | 1000000 cycles   |  |  |  |  |  |  |
| Net Weight                               | 0.665 kg   |  |  |  |  |  |  |

# **Packing Units**

Unit Type Of Package 1

PCE

| Number Of Units In Package 1 | 1         |
|------------------------------|-----------|
| Package 1 Height             | 8.500 cm  |
| Package 1 Width              | 9.000 cm  |
| Package 1 Length             | 57.000 cm |
| Package 1 Weight             | 743.000 g |
| Unit Type Of Package 2       | P06       |
| Number Of Units In Package 2 | 40        |
| Package 2 Height             | 75.000 cm |
| Package 2 Width              | 60.000 cm |
| Package 2 Length             | 80.000 cm |
| Package 2 Weight             | 42.720 kg |

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

# Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration |
| China Rohs Regulation    | China RoHS declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |


#### **Product datasheet**

XACA06

#### **Dimensions Drawings**

#### Dimensions

Below drawing shows a product with 6 cut-outs. Select the number of cut-outs according to the product characteristics in order to get b, b1 and c dimensions.



(1) For 2 and 3-way XAC A stations.

(2) For 4 to 8-way XAC A stations.

(3) With trigger action Emergency stop head operator

#### (4) Internal ø

**Dimensions in mm** Number of cut-outs b b1 С

#### Dimensions in in.

| Number of cut-outs | 2     | 3     | 4     | 5     | 6     | 8     | 12    |
|--------------------|-------|-------|-------|-------|-------|-------|-------|
| b                  | 12.36 | 12.36 | 17.32 | 17.32 | 19.68 | 22.05 | 26.77 |
| b1                 | 7.48  | 7.48  | 9.84  | 9.84  | 12.20 | 14.57 | 19.29 |

# Product datasheet

XACA06

| Number of cut-outs | 2    | 3    | 4    | 5    | 6    | 8    | 12   |
|--------------------|------|------|------|------|------|------|------|
| с                  | 3.15 | 3.15 | 3.15 | 3.15 | 3.15 | 3.15 | 3.62 |