Product datasheet

Specifications





analog input module - 1I - fullbridge strain gauge - 24 bits

TM5SEAISG

EAN Code: 3595864145150

Main

Range Of Product	Modicon TM5	
Product Or Component Type	Analog input module	
Analogue Input Number	1	
Analogue Input Type	full-bridge strain gauge 855000 Ohm differential	
Analogue Input Resolution	24 bits	

Complementary

Range Compatibility	Modicon M258 Modicon LMC058	
Product Compatibility	Logic controller Motion controller	
Maximum Number Of Sensors	4	
Colour	White	
Type Of Cable	Shielded cable	
Isolation	No insulation between channels 500 Vrms AC insulation between channel and bus	
Supply	Internal	
[Us] Rated Supply Voltage	24 V DC	
Local Signalling	LED green for power supply LED red for power supply LED green for input status	
Current Consumption	2 mA at 5 V DC bus 52 mA at 24 V DC input/output 65 mA at 5.5 V DC full-bridge (4/6 wires)	
Maximum Power Dissipation In W	ower Dissipation In W 1.25 W	
Marking	CE	
Net Weight	0.025 kg	

Environment

Temperature Drift	10 ppm/°C	
Standards	IEC 61131-2	
	CSA C22.2 No 142	
	CSA C22.2 No 213	
	UL 508	
Product Certifications	cULus	
	GOST-R	
	CSA	
	C-Tick	

Ambient Air Temperature For Operation	055 °C without derating (horizontal installation) 060 °C with derating factor (horizontal installation) 050 °C (vertical installation)		
Ambient Air Temperature For Storage	-2570 °C		
Relative Humidity	595 % without condensation		
Ip Degree Of Protection	IP20 conforming to IEC 61131-2		
Pollution Degree	2 conforming to IEC 60664		
Operating Altitude	02000 m		
Storage Altitude	03000 m		
Vibration Resistance	1 gn at 8.4150 Hz on DIN rail 3.5 mm at 58.4 Hz on DIN rail		
Shock Resistance	15 gn for 11 ms		
Resistance To Electrostatic Discharge	4 kV on contact conforming to IEC 61000-4-2 8 kV in air conforming to IEC 61000-4-2		
Resistance To Electromagnetic Fields	1 V/m 22.7 GHz conforming to IEC 61000-4-3 10 V/m 802000 MHz conforming to IEC 61000-4-3		
Resistance To Fast Transients	1 kV (I/O) conforming to IEC 61000-4-4 1 kV (shielded cable) conforming to IEC 61000-4-4 2 kV (power lines) conforming to IEC 61000-4-4		
Surge Withstand	0.5 kV differential mode conforming to IEC 61000-4-5 1 kV common mode conforming to IEC 61000-4-5		
Electromagnetic Compatibility	EN/IEC 61000-4-6		
Disturbance Radiated/Conducted	CISPR 11		

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	6.000 cm
Package 1 Length	10.500 cm
Package 1 Weight	38.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	97
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.927 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

TM5SEAISG

Dimensions Drawings

TM5 Slice

Dimensions





TM5SEAISG

Mounting and Clearance


TM5 System


Spacing Requirements






Mounting on a DIN Rail







Product datasheet

TM5SEAISG

Connections and Schema

TM5 System Wiring Recommendations


Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in.	0.35		Ω		8D -
	mm²	0,082,5	0,252,5	0,251,5	2 x 0,252 x 0,75
	AWG	2814	2414	2416	2 x 242 x 18

19 May 2024


Wiring Diagram

With a 6-Wire Full-Bridge Strain Gauge



- (1): Internal electronics
- (2): 24 Vdc I/O power segment integrated into the bus bases
- (3): 6-wire full-bridge strain gauge
- (S): Sensor

With Two 4-Wire Full-Bridge Strain Gauges



Product datasheet

TM5SEAISG

(2): 24 Vdc I/O power segment integrated into the bus bases (3): 4-wire full-bridge strain gauge