Product datasheet





pendant station XAC-A pistol grip -2 push buttons 1 Emergency stop

Local distributor code:

393522774 XACA2054

! Discontinued on: 12 Dec 2023

! End-of-service on: 12 Mar 2024

① Discontinued

EAN Code: 3389110558968

Main

Range Of Product	Harmony XAC		
Product Or Component Type	Pendant control station		
Device Short Name	XACA pistol grip		

Complementary

- · · · · · · · · · · · · · · · · · · ·		
Control Station Type	Double insulated	
Enclosure Material	Polypropylene	
Control Type	Intuitive	
Electrical Circuit Type	Control circuit	
Enclosure Type	Complete ready for use	
Control Station Application	Control of single speed hoist motor	
Control Station Composition	2 push-buttons + 1 emergency stop	
Control Button Type	Emergency stop push-button Ø 30 mm 1 NC trigger action First push-button 1 NC + 1 NO raise, slow Second push-button 1 NC + 1 NO lower, slow	
Product Compatibility	ZB2BE102 for emergency stop ZB2BE102 + ZB2BE101 for each direction	
Mechanical Interlocking	With mechanical interlocking	
Control Station Colour	Yellow	
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm^2 with or without cable end Screw clamp terminals, 2 x 1.5 mm^2 with or without cable end	
Standards	EN/ISO 13850: 2006 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60204-32 UL 508 EN/IEC 60947-5-5	
Product Certifications	UL CSA	
Protective Treatment	тн	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-4070 °C	
Vibration Resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Shock Resistance	100 gn conforming to IEC 60068-2-27	
Overvoltage Category	Class II conforming to IEC 61140	

Life Is On Schneider 5 May 2024



Ip Degree Of Protection	IP65 conforming to IEC 60529				
Ik Degree Of Protection	IK08 conforming to EN 50102				
Mechanical Durability	1000000 cycles				
Cable Entry	Rubber sleeve with stepped entry 715 mm				
Contact Code Designation	A600 AC-15, Ue = 240 V, Ie = 3 A conforming to IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A conforming to IEC 60947-5-1 appendix A				
[Ithe] Conventional Enclosed Thermal Current	10 A				
[Ui] Rated Insulation Voltage	600 V (pollution degree 3) conforming to IEC 60947-1				
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-1				
Contact Operation	Slow-break				
Maximum Resistance Across Terminals	25 MOhm				
Operating Force	1315 N				
Short-Circuit Protection	10 A fuse protection by cartridge fuse type gG				
Rated Operational Power In W	40 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 120 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 48 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 48 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 65 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 24 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C				
Terminals Description Iso N°1	(11-12)NC (13-14)NO				
Terminals Description Iso N°2	(11-12)NC				
Terminal Identifier	(11-12)NC (13-14)NO				
Net Weight	0.34 kg				

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	5 cm
Package 1 Length	30 cm
Package 1 Weight	366 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	No need of specific recycling operations		

Dimensions Drawings

Dimensions




- (1) With trigger action latching Ø 30 mm / 1.18 in. Emergency stop. (2) Internal Ø

XACA2054

Connections and Schema

Control of Single-Speed Reversing Motor




XACA2054

Performance Curves

Rated Operational Power

AC Supply 50/60 Hz Inductive Circuit

Operating rate: 3600 operating cycles/hour. Load factor: 0.5. Millions of operating cycles, AC-15 utilization category



Ithe Thermal current

(A) Current

DC Supply

Operating rate: 3600 operating cycles/hour. Load factor: 0.5.

Power broken in W for 1 million operating cycles, DC-13 utilization category

Voltage	V	24	48	120
Inductive circuit	w	65	48	40