Product datasheet

Specification





pendant station XAC-A pistol grip - 2 push buttons 1 Emergency stop

Local distributor code:

386205257 XACA2073

EAN Code: 3389110558890

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACA pistol grip

Complementary

Control Station Type	Double insulated	
Enclosure Material	Polypropylene	
Control Type	Intuitive	
Electrical Circuit Type	Control circuit	
Enclosure Type	Complete ready for use	
Control Station Application	Control of 2-speed hoist motor	
Control Station Composition	2 push-buttons + 1 emergency stop	
Control Button Type	Stop push-button Ø 30 mm 1 NC latching First push-button 2 NO (2 step) raise, slow-fast Second push-button 2 NO (2 step) lower, slow-fast	
Product Compatibility	ZB2BE102 for emergency stop ZB2BE101 + ZB2BE201 for each direction	
Mechanical Interlocking	With mechanical interlocking	
Control Station Colour	Yellow	
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm 2 with or without cable end Screw clamp terminals, 2 x 1.5 mm 2 with or without cable end	
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 UL 508 EN/IEC 60204-32	
Product Certifications	UL CSA	
Protective Treatment	тн	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-4070 °C	
Vibration Resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Shock Resistance	100 gn conforming to IEC 60068-2-27	
Overvoltage Category	Class II conforming to IEC 61140	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK08 conforming to EN 50102	

Mechanical Durability	1000000 cycles
	1000000 cycles
Cable Entry	Rubber sleeve with stepped entry 715 mm
Contact Code Designation	A600 AC-15, Ue = 240 V, Ie = 3 A conforming to IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A conforming to IEC 60947-5-1 appendix A
[Ithe] Conventional Enclosed Thermal Current	10 A
[Ui] Rated Insulation Voltage	600 V (pollution degree 3) conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-1
Contact Operation	Staggered Slow-break
Maximum Resistance Across Terminals	25 MOhm
Operating Force	1315 N
Short-Circuit Protection	10 A fuse protection by cartridge fuse type gG
Rated Operational Power In W	40 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 120 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 48 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 48 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 65 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 24 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C
Terminals Description Iso N°1	(23-24)NO_CL (13-14)NO
Terminals Description Iso N°2	(11-12)NC
Terminal Identifier	(11-12)NC (13-14)NO
Net Weight	0.36 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.700 cm
Package 1 Width	11.800 cm
Package 1 Length	34.100 cm
Package 1 Weight	363.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.935 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	120
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	58.124 kg

Contractual warranty

Warranty

5 May 2024

18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations