Product datasheet

Specifications





TeSys Mini-Vario - switch disconnector - 12 A - on door

Local distributor code: 389538594

VBDN12

EAN Code: 3389110759853

Main

Range	TeSys
Product Name	TeSys Mini-VARIO
Device Short Name	VBDN
Product Or Component Type	Switch disconnector
Performance Level	Standard
Poles Description	3P
Contacts Type And Composition	3 NO
Network Type	AC DC
Control Type	Rotary handle
Rotary Handle Mounting Style	Direct
Handle Colour	Black
Handle Front Plate Colour	Black
Rotary Handle Padlocking	1 to 3 padlocks 48 mm

Complementary

0 - 1
Handle: door
Switch: door
Hole with 22.5 mm for handle
690 V AC 50/60 Hz
6 kV
12 A
10 A
8.1 A (AC-23) at 400 V
3 kW at 230240 V (AC-23A)
4 kW at 400415 V (AC-23A)
5.5 kW at 500 V (AC-23A)
7.5 kW at 690 V (AC-23A)
1.5 kW at 230240 V (AC-3)
3 kW at 400415 V (AC-3)
4 kW at 500 V (AC-3)
4 kW at 690 V (AC-3)
30

Making Capacity (I Rms)	120 A at 400 V AC-21A
	120 A at 400 V AC-22A
	120 A at 400 V AC-23A
[Icm] Rated Short-Circuit Making	0.5 kA at 400 V at Ipeak
Capacity	
[Icw] Rated Short-Time Withstand	140 A at 400 V duration: 1 s
Rms Current	
Rated Conditional Short-Circuit	6 kA at 400 V - associated fuse 12 A aM
Current	6 kA at 400 V - associated fuse 12 A gG
	0 km at 400 V - associated luse 12 m go
Breaking Capacity	120 kA at 400 V (AC-21A)
3 1 3	120 kA at 400 V (AC-22A)
	120 kA at 400 V (AC-23A)
	120 KA at 400 V (AC-23A)
Device Composition	Switch
• • • • • • • • • • • • • • • • • • • •	Handle
Mechanical Durability	50000 cycles
Electrical Durchility	
Electrical Durability	30000 cycles DC-15
	50000 cycles AC-21
Suitability For Isolation	Yes
	165
Connections - Terminals	Power circuit: screw clamp terminals4 mm ² - flexible - with cable end
	Power circuit: screw clamp terminals4 mm ² - solid
Tightening Torque	Power circuit: 0.7 N.m - on screw clamp terminals
	·····
Handle Front Plate Dimension	60 x 60 mm
Height	60 mm
Width	60 mm
Not Waight	0.1771
Net Weight	0.177 kg

Environment

Standards	IEC 60947-3
Product Certifications	UL
	GL
	000
	CSA
	UKCA
Protective Treatment	TC
Ip Degree Of Protection	IP65
Mechanical Robustness	Vibrations 10150 Hz (5 gn) conforming to IEC 60068-2-6 Shocks 11 ms (15 gn) conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-2050 °C
Fire Resistance	960 °C conforming to IEC 60695-2-1

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	8.5 cm
Package 1 Length	12.0 cm
Package 1 Weight	178.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	24

Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.776 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations