Product datasheet

Specification





TeSys Vario enclosed, emergency switch disconnector, 115A, UL/ CSA, long handle

VC6GUN

Local distributor code: 403019698

EAN Code: 3389119413152

Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VC-GUN
Product Or Component Type	Enclosed emergency stop switch disconnector
Performance Level	High performance
Poles Description	3P
Control Type	Rotary handle
Type Of Operator	Long handle
Handle Colour	Red
Handle Front Plate Colour	Yellow
Rotary Handle Padlocking	1 to 3 padlocks 48 mm

Complementary

Marking	0 - 1
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ithe] Conventional Enclosed Thermal Current	140 A
[le] Rated Operational Current	83 A (AC-23A) at 400 V
Rated Operational Power In W	45 kW at 400 V (AC-23) 37 kW at 400 V (AC-3)
Intermittent Duty Class	30
Making Capacity (I Rms)	1750 A at 400 V AC-21A 1750 A at 400 V AC-22A 1750 A at 400 V AC-23A
[Icm] Rated Short-Circuit Making Capacity	2.8 kA at 400 V at Ipeak
[lth] Conventional Free Air Thermal Current	140.0 A conforming to IEC 690 V 115 A conforming to UL 600 V
Rated Power In Hp	50 hp at 480 V, UL certified 30 hp at 240 V, UL certified 60 hp at 600 V, UL certified
[Icw] Rated Short-Time Withstand Rms Current	2100 A at 400 V duration: 1 s
Rated Conditional Short-Circuit Current	10 kA at 400 V - associated fuse 200 A aM 10 kA at 400 V - associated fuse 200 A gG

5 May 2024 Life Is On Schneider



Breaking Capacity	1400 A at 400 V (AC-21A) 1400 A at 400 V (AC-22A)	
	1400 A at 400 V (AC-23A)	
Mechanical Durability	30000 cycles	
Electrical Durability	30000 cycles AC-21	
	30000 cycles DC-15	
Environmental Characteristic	Standard environment	
Suitability For Isolation	Yes	
Connections - Terminals	Screw clamp terminals95 mm² - solid - with cable end	
	Screw clamp terminals70 mm² - flexible	
Tightening Torque	22.6 N.m - on screw clamp terminals	
Fire Resistance	960 °C conforming to IEC 60595-2-1	
Handle Front Plate Dimension	90 x 90 mm	
Height	291 mm	
Width	241 mm	
Depth	191 mm	
Net Weight	2.19 kg	

Environment

Standards	IEC 60204 CSA C22.2 No 14 IEC 60947-4-1 UL 508
Protective Treatment	тс
Ip Degree Of Protection	IP65 conforming to IEC 60529
Nema Degree Of Protection	NEMA 12
Mechanical Robustness	Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-2050 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.0 cm
Package 1 Width	20.5 cm
Package 1 Length	30.0 cm
Package 1 Weight	3.115 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations