## **Product datasheet**

Specifications





# TeSys Vario enclosed, emergency switch disconnector, 10A, IP65

Local distributor code: 23052187

VCF02GE

EAN Code: 3389110194043

#### Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VCF
Product Or Component Type	Enclosed emergency stop switch disconnector
Performance Level	High performance
Poles Description	3P
Control Type	Rotary handle
Handle Colour	Red
Handle Front Plate Colour	Yellow
Rotary Handle Padlocking	1 to 3 padlocks 48 mm

## Complementary

eemplemental y	
Marking	0 - 1
[Ue] Rated Operational Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	8 KV
[Ithe] Conventional Enclosed Thermal Current	10 A
[le] Rated Operational Current	8.1 A (AC-23A) at 400 V
Rated Operational Power In W	4 kW at 400 V (AC-23) 3 kW at 400 V (AC-3)
Intermittent Duty Class	30
Making Capacity ( I Rms)	120 A at 400 V AC-21A 120 A at 400 V AC-22A 120 A at 400 V AC-23A
[Icm] Rated Short-Circuit Making Capacity	1 kA at 400 V at Ipeak
[Icw] Rated Short-Time Withstand Rms Current	300 A at 400 V duration: 1 s
Rated Conditional Short-Circuit Current	10 kA at 400 V - associated fuse 12 A aM 10 kA at 400 V - associated fuse 12 A gG
Breaking Capacity	120 A at 400 V (AC-21A) 120 A at 400 V (AC-22A) 120 A at 400 V (AC-23A)
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-15
Environmental Characteristic	Standard environment

Suitability For Isolation	Yes
Connections - Terminals	Screw clamp terminals10 mm² - solid Screw clamp terminals6 mm² - flexible - with cable end
Tightening Torque	2.1 N.m - on screw clamp terminals
Fire Resistance	960 °C conforming to IEC 60595-2-1
Handle Front Plate Dimension	60 x 60 mm
Height	146 mm
Width	90 mm
Depth	131 mm
Net Weight	0.5 kg

#### **Environment**

Standards	IEC 60947-4-1 IEC 60204
Protective Treatment	TC
Ip Degree Of Protection	IP65 conforming to IEC 60529
Mechanical Robustness	Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-2050 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.500 cm
Package 1 Width	11.000 cm
Package 1 Length	16.000 cm
Package 1 Weight	479.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.800 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	56
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	38.928 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations