Product datasheet

Specifications





pendant station XAC-A pistol grip -2 push buttons Local distributor code:

Local distributor code: 389858151

XACA207

EAN Code: 3389110645033

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACA pistol grip

Complementary

complementary					
Control Station Type	Double insulated				
Enclosure Material	Polypropylene				
Control Type	Intuitive				
Electrical Circuit Type	Control circuit				
Enclosure Type	Complete ready for use				
Control Station Application	Control of 2-speed hoist motor				
Control Station Composition	2 push-buttons				
Control Button Type	First push-button 2 NO (2 step) raise, slow-fast Second push-button 2 NO (2 step) lower, slow-fast				
Product Compatibility	ZB2BE101 + ZB2BE201 for each direction				
Mechanical Interlocking	With mechanical interlocking				
Control Station Colour	Yellow				
Connections - Terminals	Screw clamp terminals, $1 \times 2.5 \text{ mm}^2$ with or without cable end Screw clamp terminals, $2 \times 1.5 \text{ mm}^2$ with or without cable end				
Standards	EN/IEC 60204-32 CSA C22.2 No 14 UL 508 EN/IEC 60947-5-1				
Product Certifications	CSA UL				
Protective Treatment	ТН				
Ambient Air Temperature For Operation	-2570 °C				
Ambient Air Temperature For Storage	-4070 °C				
Vibration Resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6				
Shock Resistance	100 gn conforming to IEC 60068-2-27				
Overvoltage Category	Class II conforming to IEC 61140				
Ip Degree Of Protection	IP65 conforming to IEC 60529				
Ik Degree Of Protection	IK08 conforming to EN 50102				
Mechanical Durability	1000000 cycles				

to IEC 60947-5-1 appendix A ig to IEC 60947-5-1 appendix A ing to IEC 60947-5-1 appendix A ig to IEC 60947-5-1 appendix A			
0947-1			
0947-1			
10 A fuse protection by cartridge fuse type gG			
e <60 cyc/mn at 120 V, load factor = 5-1 appendix C e <60 cyc/mn at 48 V, load factor = 0.5 appendix C e <60 cyc/mn at 24 V, load factor = 0.5 appendix C			

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.6 cm
Package 1 Width	10.2 cm
Package 1 Length	29.1 cm
Package 1 Weight	283.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	6
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins				
Circularity Profile	No need of specific recycling operations				

Product datasheet

Dimensions Drawings


Dimensions



(1) Internal Ø

Connections and Schema

Control of 2-Speed Reversing Motor




Performance Curves

Rated Operational Power

AC Supply 50/60 Hz Inductive Circuit

Operating rate: 3600 operating cycles/hour. Load factor: 0.5. Millions of operating cycles, AC-15 utilization category



Ithe Thermal current (A) Current

DC Supply

Operating rate: 3600 operating cycles/hour. Load factor: 0.5.

Power broken in W for 1 million operating cycles, DC-13 utilization category

Voltage	V	24	48	120
Inductive circuit	w	65	48	40