Product datasheet

Specifications





pendant station XAC-A pistol grip -2 booted push buttons Local distributor code:

Local distributor code: 386205325

XACA215

EAN Code: 3389110644838

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACA pistol grip

Complementary

Complementary					
Control Station Type	Double insulated				
Enclosure Material	Polypropylene				
Control Type	Intuitive				
Electrical Circuit Type	Control circuit				
Enclosure Type	Complete ready for use				
Control Station Application	Control of single speed hoist motor				
Control Station Composition	2 booted push-buttons				
Control Button Type	First push-button 1 NC + 1 NO raise, slow Second push-button 1 NC + 1 NO lower, slow				
Product Compatibility	ZB2BE102 + ZB2BE101 for each direction				
Mechanical Interlocking	With mechanical interlocking				
Control Station Colour	Yellow				
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm ² with or without cable end Screw clamp terminals, 2 x 1.5 mm ² with or without cable end				
Standards	EN/ISO 13850: 2006 UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5				
Standards Product Certifications	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1				
	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL				
Product Certifications	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL CSA				
Product Certifications Protective Treatment Ambient Air Temperature For	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL CSA TH				
Product Certifications Protective Treatment Ambient Air Temperature For Operation Ambient Air Temperature For	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL CSA TH -2570 °C				
Product Certifications Protective Treatment Ambient Air Temperature For Operation Ambient Air Temperature For Storage	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL CSA TH -2570 °C -4070 °C				
Product Certifications Protective Treatment Ambient Air Temperature For Operation Ambient Air Temperature For Storage Vibration Resistance	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL CSA TH -2570 °C -4070 °C 15 gn (f= 10500 Hz) conforming to IEC 60068-2-6				
Product Certifications Protective Treatment Ambient Air Temperature For Operation Ambient Air Temperature For Storage Vibration Resistance Shock Resistance	UL 508 EN/IEC 60204-32 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-5 UL CSA TH -2570 °C -4070 °C 15 gn (f= 10500 Hz) conforming to IEC 60068-2-6 100 gn conforming to IEC 60068-2-27				

Mechanical Durability	1000000 cycles			
Cable Entry	Rubber sleeve with stepped entry 715 mm			
Contact Code Designation	A600 AC-15, Ue = 240 V, Ie = 3 A conforming to IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A conforming to IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A conforming to IEC 60947-5-1 appendix A			
[Ithe] Conventional Enclosed Thermal Current	10 A			
[Ui] Rated Insulation Voltage	600 V (pollution degree 3) conforming to IEC 60947-1			
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-1			
Contact Operation	Slow-break			
Maximum Resistance Across Terminals	25 MOhm			
Operating Force	1315 N			
Short-Circuit Protection	10 A fuse protection by cartridge fuse type gG			
Rated Operational Power In W	40 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 120 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 48 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 48 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C 65 W DC-13 for 1000000 cycles, operating rate <60 cyc/mn at 24 V, load factor = 0.5 (inductive load) conforming to IEC 60947-5-1 appendix C			
Terminals Description Iso N°1	(13-14)NO (11-12)NC			
Terminal Identifier	(11-12)NC (13-14)NO			
Net Weight	0.32 kg			

Packing Units

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.100 cm
Package 1 Width	8.900 cm
Package 1 Length	30.600 cm
Package 1 Weight	292.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.885 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	120
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	49.844 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Product datasheet

Dimensions Drawings

Dimensions




(1) Internal Ø

Product datasheet

Connections and Schema

Control of Single-Speed Reversing Motor




Performance Curves

Rated Operational Power

AC Supply 50/60 Hz Inductive Circuit

Operating rate: 3600 operating cycles/hour. Load factor: 0.5. Millions of operating cycles, AC-15 utilization category



Ithe Thermal current (A) Current

DC Supply

Operating rate: 3600 operating cycles/hour. Load factor: 0.5. Power broken in W for 1 million operating cycles, DC-13 utilization category

Voltage	V	24	48	120
Inductive circuit	w	65	48	40