# **Product datasheet**

Specifications





## die-cast empty control station -XAPM - Ø 22 - zinc alloy - 2 openings

XAPM1502H29

- () Discontinued on: 30 Jun 2022
- (!) End-of-service on: 18 Apr 2024

#### EAN Code: 3389110312652

#### Main

armony XAP ie-cast empty control station APM or Ø 22 mm control and signalling units					
APM or Ø 22 mm control and signalling units					
or Ø 22 mm control and signalling units					
80 x 80 mm					
74.5 mm					
2 cut-outs					
lue					
lue					
inc alloy					
1 hole with blanking plug for ISO 429248 cable gland, clamping capacity: 20 mm 1 hole without blanking plug for ISO 429248 cable gland, clamping capacity: 20 m					
lush					
P65 conforming to IEC 60529 P69 conforming to NF C 20-010 P69K					

#### Complementary

Number Of Vertical Rows	2				
Net Weight	0.6 kg				

#### Environment

Protective Treatment	TC				
Ambient Air Temperature For Storage	-4070 °C				
Ambient Air Temperature For Operation	-4070 °C				
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030				

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	8.2 cm	
Package 1 Width	9.2 cm	
Package 1 Length	9.4 cm	
Package 1 Weight	782 g	

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

#### **Dimensions Drawings**

#### **Dimensions and Fixing**



(1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity

(2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity

- (3)  $2 \times \emptyset 5.6 \text{ mm}/0.22 \text{ in. holes, depth } 20 \text{ mm}/0.78 \text{ in.}$
- P Usable depth

а		b		С		G		Н		Р	
mm	in.	mm	in.								
80	3.15	80	3.15	77	3.03	50	1.97	65	2.56	74.5	2.93

Refer to the product characteristics to get the number of cut-outs. **Cut-out interaxis dimensions** 



b2 Horizontal interaxis: 30 mm/1.18 in.