



die-cast empty control station -XAPM - Ø22- zinc alloy- 4 openings in 2 columns

Local distributor code: 393523304

XAPM2504

Discontinued on: 18 Apr 2024

! Discontinued

EAN Code: 3389110312942

Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	XAPM					
Product Destination	For Ø 22 mm control and signalling units					
Product Front Plate Size	80 x 130 mm					
Usable Depth	74.5 mm					
Number Of Cut-Out	4 cut-outs					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
Material	Zinc alloy					
Cable Entry	1 hole with blanking plug for cable gland, clamping capacity: 14 mm 1 hole without blanking plug for cable gland, clamping capacity: 14 mm					
Device Mounting	Flush					
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP69 conforming to NF C 20-010 IP69K					

Complementary

Number Of Vertical Rows	2
Net Weight	0.81 kg

Environment

Protective Treatment	TC			
Ambient Air Temperature For Storage	-4070 °C			
Ambient Air Temperature For Operation	-4070 °C			
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030			

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm

Package 1 Width	9 cm
Package 1 Length	15.5 cm
Package 1 Weight	1 006 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Dimensions and Fixing




- (1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.
- P Usable depth

а		b		С		G		H		P		
	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
	80	3.15	130	5.12	77	3.03	50	1.97	115	4.53	74.5	2.93

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions (vertical mounting)



- b1 Vertical interaxis: 40 mm/1.57 in.
- b2 Horizontal interaxis: 30 mm/1.18 in.