Product datasheet

3

(!) Discontinued

Specifications



empty control station - XAP-M zinc alloy - without opening Local distributor code: 22489052

XAPM34H29

() Discontinued on: 18 Apr 2024

EAN Code: 3389118115408

Main					
Range Of Product	Harmony XAP				
Product Or Component Type	Die-cast empty control station				
Device Short Name	ХАРМ				
Product Front Plate Size	80 x 175 mm				
Usable Depth	74.5 mm				
Number Of Cut-Out	Undrilled				
Colour Of Base Of Enclosure	Blue				
Colour Of Cover	Blue				
Material	Zinc alloy				
Cable Entry	1 hole with blanking plug for ISO 429248 cable gland, clamping capacity: 25 mm 1 hole without blanking plug for ISO 429248 cable gland, clamping capacity: 25 mm				
Product Mounting	Flush mounting				
Ip Degree Of Protection	IP65 conforming to IEC 60529				

Complementary

Net Weight

1.16 kg

Environment

Protective Treatment	тс					
Ambient Air Temperature For Storage	-4070 °C					
Ambient Air Temperature For Operation	-4070 °C					
Electrical Shock Protection Class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030					

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	12 cm
Package 1 Length	18.5 cm
Package 1 Weight	1.338 kg

Contractual warranty

Warranty

18 months



Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Dimensions and Fixing



(1) 1 hole, without blanking plug, for cable gland with 18 mm/0.71 in. maximum clamping capacity

(2) 1 hole, with blanking plug (protrusion 6 mm/0.24 in.), for cable gland with 18 mm/0.71 in. maximum clamping capacity

а		b		С		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	175	6.89	77	3.03	50	1.97	160	6.30	74.5	2.93

(3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.